


Transmittal, reproduction, dissemination and/or editing of this document as well as the use of its content for purposes not intended by the manufacturer without express authorization are prohibited. Infringers will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.



- 1) Protected centre hole M10x24
- 2) Relief groove as per DIN509 / IS:3428
- 3) Measured across screw heads

Tolerance DIN EN 50347 Untolerated Dimensions- ISO 2768v / IS2102v	Surface	Material	Weight	Scale
			-	mm
FS.:100L; Const.:IMB3 1LE7503-1AC42-3AA4 -	Author	Dimensional drawing		
	Creator DTK			
	Approval			
	Department			
SIEMENS	Change Order	MLFB	Doc. Type	
	Doc. State 5/21/24	Item No	Paper Size	A4
	Revision Index RS	Doc. No	Language	en
	Project No -	Ref. No -	Sheet	1 of 1
© Siemens AG 2023				