




- 1) Protected centre hole M16x36
- 2) Relief groove as per DIN509 / IS:3428
- 3) Measured across screw heads

|                                                                          |              |                     |         |            |
|--------------------------------------------------------------------------|--------------|---------------------|---------|------------|
| Tolerance<br>DIN EN 50347<br>Untolerated Dimensions- ISO 2768v / IS2102v | Surface      | Material            | Weight  | Scale      |
|                                                                          |              |                     | -       | mm         |
| FS.:160M; Const.:IMB3<br>1LE7503-1DB23-5AA4                              | Author       | Dimensional drawing |         |            |
|                                                                          | Creator      |                     |         |            |
| -                                                                        | Approval     | DTK                 |         |            |
|                                                                          | Department   |                     |         |            |
|                                                                          | Change Order | MLFB                |         |            |
|                                                                          | Doc. State   |                     |         |            |
| SIEMENS                                                                  | Revision     | 5/21/24             | Item No | Paper Size |
|                                                                          | Index        | RS                  | Doc No  | Language   |
| © Siemens AG 2023                                                        | Project No   | -                   | Ref No  | Sheet      |
|                                                                          |              |                     |         | 1 of 1     |