

[illegible]

- | | | | | |
|---|---------------------------------|---------------------|-------------|---|
| Tolerance
DIN EN 50347
Untolerated Dimensions- ISO 2768v / IS2102v | Surface | Material | Weight
- | Scale
 mm |
| FS.:225S; Const.:1MB3
1LE7503-2BB03-5AA4
- | Author | Dimensional drawing | | |
| | Creator
<div>DTK</div> | | | |
| | Approval | | | |
| | Department | | | |
| | Change Order | | | |
|  | Doc State
<div>5/21/24</div> | MFB | Doc Type | |
| | Revision
<div>Index RS</div> | Item No | Paper Size | A4 |
| | | Doc No | Language | en |
| © Siemens AG 2023 | Project No - | Ref No - | Sheet | 1 of 1 |

SIEMENS