SIEMENS

Data sheet for SINUMERIK Machine control panel




Figure similar

MLFB-Ordering data **6FC5303-0AF33-0AA1**

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input voltage	DC 5 V
Power consumption, max.	2.5 W

Mechanical data

Net weight	1.100 kg (2.43 lb)
Width	310.0 mm (12.20 in)
Height	175.0 mm (6.89 in)
Depth	54.0 mm (2.13 in)

Degree of protection

Rear side	IP00
Front side	IP65

Ambient conditions

Climate class according to EN60721-3-3	Condensation and icing excluded. Low air temperature 0 °C (32 °F).

Ambient temperature

Operation on the front	0 ... 45 °C (32 ... 113 °F)
Operation at the rear	0 ... 55 °C (32 ... 131 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity

Operation	5 ... 90 %
Storage	5 ... 95 %
Transport	5 ... 95 %

Approvals

Certificate of suitability	CE, cULus, EAC, KCC, RCM

Technical data are subject to change! There may be discrepancies between calculated and rating plate values.