

MOTION CONNECT 500

MLFB-Ordering data

6FX5002-5CG21-1AB0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data

|                                          |              |
|------------------------------------------|--------------|
| No. of cores x cross-section mm²         | 4x1.5 C      |
| Test voltage, rms Power conductors       | 4.0 kV       |
| Test voltage, rms Signal conductors      | 2.0 kV       |
| Type with braking lead                   | No           |
| Rated voltage V0/V according to EN 50395 | 600 V/1000 V |

Mechanical data

|                                         |                      |
|-----------------------------------------|----------------------|
| Type of connection cable engine side    | Conector full thread |
| Connector size                          | 1.5 / M40            |
| Type of bolting                         | not relevant         |
| Type of connection cable converter side | Open end of lead     |
| Maximum cable outer diameter            | 8.4 mm               |
| Length                                  | 1.0 m                |
| Weight (without connector)              | 0.1 kg               |

Static deployment

|                                                    |                         |
|----------------------------------------------------|-------------------------|
| Smallest bending radius (fixed installation)       | 21.0 mm                 |
| Tensile load for permanently installed cable, max. | 50 N/mm² (7252 lbf/in²) |
| Torsional stress                                   | Absolute 30°/m          |

Dynamic deployment

|                                                                    |                         |
|--------------------------------------------------------------------|-------------------------|
| Smallest bending radius(flexible installation in a cable carriers) | 155.0 mm                |
| Acceleration horizontal, max                                       | 2 m/s²                  |
| Maximum traversing velocity                                        | 30 m/min                |
| Travel path                                                        | 5 m                     |
| Number of bends, max.                                              | 100,000                 |
| Tensile load for moving cable, max.                                | 20 N/mm² (2901 lbf/in²) |



Figure similar

MLFB-Ordering data

6FX5002-5CG21-1AB0

Technical data

Ambient temperature

|                                                         |                                         |
|---------------------------------------------------------|-----------------------------------------|
| Operation with permanently installed cable              | -20 ... 80 °C                           |
|                                                         | Module-end power connector 0 ... 55°C   |
| Operation with moving cable                             | 0 ... 60 °C                             |
|                                                         | Module-end power connector 0 ... 55°C   |
| Storage                                                 | -20 ... 80 °C                           |
|                                                         | Module-end power connector -20 ... 70°C |
| Kind of connection cable                                | Basis cable                             |
| Material of the cable sheath                            | PVC DESINA color orange RAL 2003        |
| Type of insulation                                      | CFC/silicone-free                       |
| Standard for behavior in fire: flame resistance         | EN 60332-1-1 to 1-3                     |
| Oil resistance                                          | EN 60811-2-1 (mineral oil only)         |
| Verification of suitability as authorisation for USA    | UL758                                   |
| Verification of suitability as authorisation for Canada | CSA-C22.2-N.210.2-M90                   |