



Figure similar

MOTION CONNECT 800PLUS

MLFB-Ordering data 6FX8002-8QN04-1BD0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Electrical data

|                                          |                            |
|------------------------------------------|----------------------------|
| No. of cores x cross-section mm²         | 4x0.38 + 4x0.2 + 2x0.38C C |
| Test voltage, rms Power conductors       | 1.5 kV                     |
| Test voltage, rms Signal conductors      | 0.5 kV                     |
| Type with braking lead                   | Yes                        |
| Rated voltage V0/V according to EN 50395 | 300 V                      |

Mechanical data

|                                         |                                                              |
|-----------------------------------------|--------------------------------------------------------------|
| Type of connection cable engine side    | Conector SPEED-CONNECT                                       |
| Connector size                          | M12                                                          |
| Type of bolting                         | not relevant                                                 |
| Type of connection cable converter side | Wire ends with ferrules (OCC signal connector pre-assembled) |
| Maximum cable outer diameter            | 9.7 mm                                                       |
| Length                                  | 13.0 m                                                       |
| Weight (without connector)              | 1.69 kg                                                      |

Static deployment

|                                              |                         |
|----------------------------------------------|-------------------------|
| Smallest bending radius (fixed installation) | 28.2 mm                 |
| Tensile stress, max. Fixed installation      | 50 N/mm² (7252 lbf/in²) |
| Torsional stress                             | Absolute 30°/m          |

Dynamic deployment

|                                                                    |                         |
|--------------------------------------------------------------------|-------------------------|
| Smallest bending radius(flexible installation in a cable carriers) | 38.0 mm                 |
| Acceleration horizontal, max                                       | 50 m/s²                 |
| Maximum traversing velocity                                        | 300 m/min               |
| Travel path                                                        | 50 m                    |
| Number of bends, max.                                              | 10,000,000              |
| Tensile load for moving cable, max.                                | 20 N/mm² (2901 lbf/in²) |



Figure similar

MLFB-Ordering data

6FX8002-8QN04-1BD0

Technical data

Ambient temperature

|                                            |                                                                                 |
|--------------------------------------------|---------------------------------------------------------------------------------|
| Operation with permanently installed cable | -20 ... 80 °C                                                                   |
|                                            | Module-end power connector 0 ... 55°C, Motor-end power connector -20 ... 80°C   |
| Operation with moving cable                | -20 ... 60 °C                                                                   |
|                                            | Module-end power connector 0 ... 55°C                                           |
| Storage                                    | -20 ... 80 °C                                                                   |
|                                            | Module-end power connector -20 ... 70°C, Motor-end power connector -20 ... 80°C |

|                                                         |                                  |
|---------------------------------------------------------|----------------------------------|
| Kind of connection cable                                | Basis cable                      |
| Material of the cable sheath                            | PUR DESINA color orange RAL 2003 |
| Type of insulation                                      | CFC/halogen/silicone-free        |
| Standard for behavior in fire: flame resistance         | EN 60332-1-1 to 1-3              |
| Oil resistance                                          | EN 60811-2-1                     |
| Verification of suitability as authorisation for USA    | UL 758                           |
| Verification of suitability as authorisation for Canada | CSA-C22.2-N.210.2-M90            |