SIEMENS

Data sheet for Absolute encoder



Figure similar

MLFB-Ordering data **6FX2001-5QS12**

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data

Operating voltage Up	DC 10 ... 30 V
Max. power consumption	160 mA
Interface	SSI
Clock input	Differential line receiver according to EIA Standard RS 485
Data output	Differential line driver according to EIA Standard RS 485
Short-circuit strength	Yes
Transmission rate	100 kHz ... 1 MHz
Connection type	Flange socket, Radial
Resolution	13 bit (8192 increments)
Telegram	13 bit, without parity

Code type

Sampling	Gray
Transmission	Gray, fir-tree format

Parameterizability

Preset	Yes
Counting direction	Yes
Accuracy	± 79 " (with 8192 increments)

Cable length up to the subsequent electronics, max.

Up to 100 kHz	400.0 m
Up to 300 kHz	100.0 m
Up to 1 MHz	50.0 m

Mechanical data

Shaft version	Solid shaft
Shaft diameter	10 mm
Shaft length	20 mm
Angular acceleration, max.	100000 rad/s²
Moment of inertia of rotor	0.00000145 kgm²
Vibration (55...2000 Hz), max.	300 m/s²
Friction torque (at 20°C)	<= 0.01 Nm
Starting torque (at 20°C)	<= 0.01 Nm
Net weight	0.3 kg

Speed max.

With ± 1 bit accuracy	5000 rpm
With ± 100 bit accuracy	10000 rpm
Max. permissible speed (mech.)	12000 rpm

Load capacity

n <= 6000 rpm	
- Axial	40 N
- Radial at shaft end	60 N
n > 6000 rpm	
- Axial	10 N
- Radial at shaft end	20 N

Shock, max.

2 ms	2000 m/s²
6 ms	1000 m/s²

Degree of protection

Without shaft input	IP67
With shaft input	IP64

Technical data are subject to change! There may be discrepancies between calculated and rating plate values.

SIEMENS

Data sheet for Absolute encoder

MLFB-Ordering data **6FX2001-5QS12**



Figure similar

Ambient temperature

During operation	-40 ... 85 °C

Standards

Compliance with standards	CE, cULus
EMC class filter	Tested to DIN EN 50081 and EN 50082