



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data

Operating voltage Up	DC 10 ... 30 V
Max. power consumption	130 ... 400 mA (< 4 W)
Interface	PROFINET IO with RT / IRT
Clock input	2 ports IRT
Data output	2 ports IRT
Short-circuit strength	Yes
Transmission rate	100 Mbit/s
LED for diagnostics	Yes (green/red/yellow)
Connection type	2 x connector M12, 4-pin for PROFINET / EtherNet/IP Ports, 1 x connector M12, 4-pin for operating voltageRadial
Resolution	27 bit (8192 increments x 16384 rpm)

Telegram

According to PNO cncoder profile V4.1
Class1, Class 2, Class 3, Class 4,
standard telegrams 81/82/83/84,
Siemens telegram 860

Code type

Sampling	Gray
Transmission	binary, PROFINET / EtherNet/IP

Cable length up to the subsequent electronics, max.

Up to 12 Mbit/s	100 m
-----------------	-------

Mechanical data

Shaft version	Hollow shaft
Shaft diameter	15 mm (8 mm / 10 mm / 12 mm with reducing sleeves)
Angular acceleration, max.	100000 rad/s ²
Moment of inertia of rotor	0.00000301 kgm ²
Vibration (55...2000 Hz), max.	100 m/s ²
Friction torque (at 20°C)	<= 0.01 Nm
Starting torque (at 20°C)	<= 0.01 Nm
Net weight	0.4 kg

Speed max.

With ± 1 bit accuracy	5800 rpm
Max. permissible speed (mech.)	6000 rpm

Load capacity

n <= 6000 rpm	
- Axial	40 N
- Radial at shaft end	110 N

n > 6000 rpm	
- Axial	10 N
- Radial at shaft end	20 N

Shock, max.

2 ms	2000 m/s ²
6 ms	1000 m/s ²

Degree of protection

Without shaft input	IP67
With shaft input	IP64

MLFB-Ordering data

6FX2001-5WN25



Figure similar

Electrical data		Ambient temperature	
Parameterizability		During operation	-40 ... 85 °C
Preset	Yes	Standards	
Counting direction	Yes	Compliance with standards	CE, cULus
Resolution per revolution	Any 1 ... 8192	EMC class filter	Tested to DIN EN 50081 and EN 50082
Total resolution	Any 1 ... 8192 x 16384		
Speed signal	Yes		
Limit switch	No		
Clock synchronism	Yes		
Slave-to-slave communication	No		
Accuracy	± 79 " with 8192 increments (± 1/2 LSB)		