



Figure similar

MLFB-Ordering data 6FX2001-5VD13-1AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 24 V - 15 % + 20 %	Shaft version	Hollow shaft
Max. power consumption	37 mA	Shaft diameter	10 mm
Interface	DRIVE-CLiQ	Shaft length	24 mm
Data output	DRIVE-CLiQ	Angular acceleration, max.	100000 rad/s²
Short-circuit strength	Yes	Vibration (55...2000 Hz), max.	150 m/s²
Transmission rate	100 Mbit/s	Friction torque (at 20°C)	<= 0.01 Nm
Cable length up to the subsequent electronics, max.	100 m	Starting torque (at 20°C)	<= 0.01 Nm
Connection type	Flange socket, Radial	Net weight	0.3 kg
Resolution	24 bit	Max. admissible speed	
Incremental track	2048 S/R, 1 Vpp (encoder-internal only)	Electrical	14000 rpm
Accuracy	± 20 "	Mechanical	15000 rpm
Code type		Load capacity	
Sampling	Gray	n <= 6000 rpm	
Transmission	DRIVE-CLiQ	- Axial	40 N
		- Radial at shaft end	60 N
		n > 6000 rpm	
		- Axial	10 N
		- Radial at shaft end	20 N
Ambient temperature		Shock, max.	
During operation	-30 ... 100 °C	6 ms	1000 m/s²
Standards		Degree of protection	
Compliance with standards	CE, cULus	Without shaft input	IP67
EMC class filter	Tested to DIN EN 50081 and EN 50082	With shaft input	IP64