



Figure similar

MLFB-Ordering data 6SE6430-2UD38-8FA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

| Rated data | | General tech. specifications | |
|----------------------------------|--------------------------|------------------------------|---------------|
| Input | | Power factor λ | 0.95 |
| Number of phases | 3 AC | Efficiency η | 0.96 |
| Line voltage | 380 ... 480 V $\pm 10\%$ | Ambient conditions | |
| Line frequency | 47 ... 63 Hz | Cooling | Fan |
| Rated current (LO) | 169.00 A | Ambient temperature | |
| Output | | Operation (LO) | -10 ... 40 °C |
| Number of phases | 3 AC | Transport | -40 ... 70 °C |
| Rated voltage | 480 V | Storage | -40 ... 70 °C |
| Rated power (LO) | 90.00 kW / 120.00 hp | | |
| Rated current (LO) | 178.00 A | | |
| Pulse frequency | 4000 Hz | | |
| Output frequency for V/f control | 0 ... 650 Hz | | |

As a result of legal stipulations, a limit to 550 Hz is in production

Overload capability

Low Overload (LO)

140 % output current for 3 s, followed by 110 % output current for 57 s followed by 100 % output current for 240 s in a 300 s cycle time

MLFB-Ordering data 6SE6430-2UD38-8FA0



Figure similar

| Mechanical data | | Connections | |
|----------------------|---------------------|-------------------------|------------|
| Degree of protection | IP20 / UL open type | Motor end | |
| Frame size | FSF | Conductor cross-section | 150.00 mm² |
| Net weight | 56.00 kg | | |
| Width | 350.0 mm | | |
| Height | 850.0 mm | | |
| Depth | 320.0 mm | | |

| Inputs / outputs | |
|-------------------------|---|
| Standard digital inputs | |
| Number | 6 |
| Relay output | |
| Number | 3 |
| Analog inputs | |
| Number | 2 |
| Analog outputs | |
| Number | 2 |
| PTC/ KTY interface | |
| Number | 1 |