SIEMENS

Data sheet for MICROMASTER 440



Figure similar

MLFB-Ordering data

6SE6440-2UC21-1BA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	1 / 3 AC
Line voltage	200 ... 240 V ±10 %
Line frequency	47 ... 63 Hz
Rated current (HO)	11.00 A / 6.40 A

Output

Number of phases	3 AC
Rated voltage	240 V
Rated power (HO)	1.10 kW / 1.50 hp
Rated current (HO)	5.50 A
Pulse frequency	16000 Hz
Output frequency for V/f control	0 ... 650 Hz

As a result of legal stipulations, a limit to 550 Hz is in production

Overload capability

High Overload (HO)

150 % output current for 60 s, followed by 100 % output current for 240 s in a 300 s cycle time

General tech. specifications

Power factor λ	0.95
Efficiency η	0.96

Ambient conditions

Cooling	Fan

Ambient temperature

Operation (HO)	-10 ... 50 °C
Transport	-40 ... 70 °C
Storage	-40 ... 70 °C

SIEMENS

Data sheet for MICROMASTER 440

MLFB-Ordering data **6SE6440-2UC21-1BA1**



Figure similar

Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSB
Net weight	3.30 kg
Width	149.0 mm
Height	202.0 mm
Depth	172.0 mm

Inputs / outputs

Standard digital inputs

Number	6

Relay output

Number	3

Analog inputs

Number	2

Analog outputs

Number	2

PTC/ KTY interface

Number	1

Connections

Motor end

Conductor cross-section	6.00 mm²

Technical data are subject to change! There may be discrepancies between calculated and rating plate values.