SIEMENS

Data sheet for MICROMASTER 430



Figure similar

MLFB-Ordering data

6SE6430-2UD41-1FA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V ±10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	200.00 A

Output

Number of phases	3 AC
Rated voltage	480 V
Rated power (LO)	110.00 kW / 150.00 hp
Rated current (LO)	205.00 A
Pulse frequency	2000 Hz
Output frequency for V/f control	0 ... 267 Hz

Overload capability

Low Overload (LO)

150 % output current for 1 s, followed by 110 % output current for 59 s followed by 100 % output current for 240 s in a 300 s cycle time

General tech. specifications

Power factor λ	0.95
Efficiency η	0.97

Ambient conditions

Cooling	Fan

Ambient temperature

Operation (LO)	0 ... 40 °C
Transport	-40 ... 70 °C
Storage	-40 ... 70 °C

SIEMENS

Data sheet for MICROMASTER 430

MLFB-Ordering data **6SE6430-2UD41-1FA0**



Figure similar

Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FX
Net weight	116.00 kg
Width	326.0 mm
Height	1400.0 mm
Depth	356.0 mm

Inputs / outputs

Standard digital inputs

Number	6

Relay output

Number	3

Analog inputs

Number	2

Analog outputs

Number	2

PTC/ KTY interface

Number	1

Connections

Motor end

Conductor cross-section	185.00 mm²