



Figure similar

MLFB-Ordering data                      6SE6440-2UC34-5FA1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		General tech. specifications	
Input		Power factor $\lambda$	0.95
Number of phases	3 AC	Efficiency $\eta$	0.96
Line voltage	200 ... 240 V $\pm 10\%$	Ambient conditions	
Line frequency	47 ... 63 Hz	Cooling	Fan
Rated current (LO)	164.00 A	Ambient temperature	
Rated current (HO)	135.00 A	Operation (LO)	-10 ... 40 °C
Output		Operation (HO)	-10 ... 50 °C
Number of phases	3 AC	Transport	-40 ... 70 °C
Rated voltage	240 V	Storage	-40 ... 70 °C
Rated power (LO)	55.00 kW / 75.00 hp		
Rated power (HO)	45.00 kW / 60.00 hp		
Rated current (LO)	178.00 A		
Rated current (HO)	154.00 A		
Pulse frequency	4000 Hz		
Output frequency for V/f control	0 ... 650 Hz		

As a result of legal stipulations, a limit to 550 Hz is in production

### Overload capability

#### Low Overload (LO)

140 % output current for 3 s, followed by 110 % output current for 57 s followed by 100 % output current for 240 s in a 300 s cycle time

#### High Overload (HO)

150 % output current for 60 s, followed by 100 % output current for 240 s in a 300 s cycle time

MLFB-Ordering data                      6SE6440-2UC34-5FA1



Figure similar

Mechanical data		Connections	
Degree of protection	IP20 / UL open type	Motor end	
Frame size	FSF	Conductor cross-section	150.00 mm²
Net weight	56.00 kg		
Width	350.0 mm		
Height	850.0 mm		
Depth	320.0 mm		

Inputs / outputs	
Standard digital inputs	
Number	6
Relay output	
Number	3
Analog inputs	
Number	2
Analog outputs	
Number	2
PTC/ KTY interface	
Number	1