

MLFB-Ordering data 6SL3100-0BE23-6AB0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data		General tech. specifications	
Input		Sound pressure level	60 dB
Number of phases	3 AC	Power loss	0.34 kW
Line voltage	380 ... 480 V	Ambient conditions	
Internal resistor	1440 Ω +10% -10%	Type of cooling	Internal air cooling
Rated data		Cooling air throughput	0.04 m³/s (1.41 ft³/s)
Rated current	58 A	Standards	
Power requirement (DC 24 V)	0.49 A	Compliance with standards	cURus
Switching current (as NC circuit at 250 V AC)	1.6 A	Connections	
Switching current (as NC circuit at 60 V DC)	0.75 A	Line side	
Mechanical data		Version	screw-type terminal
Dimensions		Conductor cross-section	50 mm² (1 AWG)
Width	150 mm (5.91 in)	PE conductor	M6 screw
Height	380 mm (14.96 in)		
Depth	270 mm (10.63 in)		
Degree of protection	IP20 / UL open type		
Net weight	19.00 kg (41.89 lb)		
Type of construction	Booksize		