



Figure similar

Data sheet for Smart Line Modules Booksize

Article No. : 6SL3130-6AE15-0AB1

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Electrical data

Input	
Number of phases	3 AC
Line voltage	342 ... 528 V
Line frequency	47 ... 63 Hz
Short-circuit strength <sup>1)</sup>	65 kA
Line power factor	
Fundamental power factor, minimal	.96
Total	0.65 ... 0.90
Overvoltage category	Class III
DC link voltage <sup>2)</sup>	
DC-link voltage	1.35 × line voltage
Electronics power supply with DC	24 V (-15 % / 20 %)

Connections

Line side	
Design	screw-type terminal (X1)
Conductor cross-section	2.5 ... 6 mm <sup>2</sup> (AWG 14 ... AWG 10)
PE conductor	M5 screw
Shield connecting kit	Cable shield connection plate integrated into the connector
Line length, max.	
Shielded	350 m (1,148.29 ft)
Unshielded	560 m (1,837.27 ft)

Mechanical data

Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	4.7 kg (10.36 lb)
Dimensions	
Width	50 mm (1.97 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Standards

Compliance with standards	CE, cULus
---------------------------	-----------

Rated data

Infeed power	
Rated value	5.0 kW (5.0 hp)
for S6 duty	6.5 kW
Maximum	10.0 kW
Regenerative feedback power	
Rated value	5.0 kW (5.0 hp)
for S6 duty	6.5 kW
Maximum	10.0 kW
DC-link current	
at 540 V DC	9.3 A
at 600 V DC	8.3 A
for S6 duty	11.0 A
Maximum	16.6 A
Input current	
at 380 V AC 3-phase	8.6 A
at 400 V AC 3-phase	8.1 A
at 480 V AC 3-phase	6.7 A
at 400 V S6 duty	10.6 A
at 400 V, maximum	15.7 A
Current requirement at 24 V DC, maximum	0.80 A
Ampacity of the busbars	
for electronics power supply at 24 V DC	20 A
for DC-link connection	100 A
DC link capacitance	
of the Smart Line Module	220 µF
of the drive system, maximum	6,000 µF

General technical specifications

Sound pressure level	60 dB
Losses <sup>4)</sup>	0.080 kW

Ambient conditions

Ambient temperature in operation	0 ... 40 °C (32 ... 104 °F)
Cooling air throughput	0.008 m <sup>3</sup> /s (0.283 ft <sup>3</sup> /s)
Installation altitude	1,000 m (3,280.84 ft)
Type of cooling	Internal air cooling
RI suppression	Standard: No radio interference suppression; With line filter: Category C2 to EN 61800-3 Total cable length up to 350 m (1148 ft) (shielded)

<sup>1)</sup>in conjunction with the recommended Class J fuse, or circuit breaker according to UL489 / CSA 22.2 No. 5-02  
<sup>2)</sup>The DC link voltage is maintained at the mean value of the rectified line voltage.  
<sup>4)</sup>Power loss of the Smart Line Module with rated power including losses of the 24 V DC electronics power supply