



Figure similar

Data sheet for Smart Line Modules Booksize

Article No. : 6SL3130-6TE23-6AA3

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Electrical data	
Input	
Number of phases	3 AC
Line voltage	342 ... 528 V
Line frequency	47 ... 63 Hz
Short-circuit strength <sup>1)</sup>	65 kA
Line power factor	
Fundamental power factor, minimal	.96
Total	0.65 ... 0.90
Overvoltage category	Class III
DC link voltage <sup>2)</sup>	
DC-link voltage	1.35 × line voltage
Electronics power supply with DC	24 V (-15 % / 20 %)

Connections	
Line side	
Design	M6 bolt (X1)
Conductor cross-section	2.5 ... 50 mm <sup>2</sup> (AWG 14 ... AWG 1)
PE conductor	M6 screw
Line length, max.	
Shielded	630 m (2,066.93 ft)
Unshielded	850 m (2,788.71 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	10.0 kg (22.05 lb)
Dimensions	
Width	150 mm (5.91 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Standards	
Compliance with standards	CE, cULus

Rated data	
Infeed power	
Rated value	36.0 kW (40.0 hp)
for S6 duty	47.0 kW
Maximum	70.0 kW
Regenerative feedback power	
Rated value	36.0 kW (40.0 hp)
for S6 duty	47.0 kW
Maximum	70.0 kW
DC-link current	
at 540 V DC	67.0 A
at 600 V DC	60.0 A
for S6 duty	79.0 A
Maximum	118.0 A
Input current	
at 380 V AC 3-phase	62.0 A
at 400 V AC 3-phase	59.0 A
at 480 V AC 3-phase	51.0 A
at 400 V S6 duty	76.0 A
at 400 V, maximum	112.0 A
Current requirement at 24 V DC, maximum	1.50 A
Ampacity of the busbars	
for electronics power supply at 24 V DC	20 A
for DC-link connection	200 A
DC link capacitance	
of the Smart Line Module	1,410 µF
of the drive system, maximum	20,000 µF

General technical specifications	
Sound pressure level	65 dB
Losses <sup>4)</sup>	0.406 kW
Ambient conditions	
Ambient temperature in operation	0 ... 40 °C (32 ... 104 °F)
Cooling air throughput	0.031 m <sup>3</sup> /s (1.095 ft <sup>3</sup> /s)
Installation altitude	1,000 m (3,280.84 ft)
Type of cooling	Internal air cooling
RI suppression	Standard: No radio interference suppression; With line filter: Category C2 to EN 61800-3 Total cable length up to 350 m (1148 ft) (shielded)

<sup>1)</sup>in conjunction with the recommended Class J fuse, or circuit breaker according to UL489 / CSA 22.2 No. 5-02  
<sup>2)</sup>The DC link voltage is maintained at the mean value of the rectified line voltage.  
<sup>4)</sup>Power loss of the Smart Line Module with rated power including losses of the 24 V DC electronics power supply