

Article No. : 6SL3130-7TE25-5AA3

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Figure similar



Electrical data	
Input	
Number of phases	3 AC
Line voltage	342 ... 528 V
Line frequency	47 ... 63 Hz
Short-circuit strength <sup>1)</sup>	65 kA
Line power factor	
in Active mode	
Fundamental power factor cos phi <sub>1 2)</sub>	1
Total	1
in Smart Mode	
Fundamental power factor, minimal	.96
Total	0.65 ... 0.90
Overvoltage category	Class III
DC link voltage <sup>3)</sup>	
at 380 V ... 400 V AC, factory setting	600 V
at 400 V ... 415 V AC, factory setting	625 V
DC-link voltage	1.35 x line voltage (Smart Mode)
Electronics power supply with DC	24 V (-15 % / 20 %)

Connections	
Line side	
Design	M8 bolt (X1)
Conductor cross-section	2.50 ... 95.00 mm <sup>2</sup> (AWG 14 ... AWG -2) (Alternatively 2 x 35 mm <sup>2</sup> )
PE conductor	M6 screw
Line length, max.	
Shielded	1,000 m (3,280.84 ft)
Unshielded	1,500 m (4,921.26 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	17.0 kg (37.48 lb)
Dimensions	
Width	200 mm (7.87 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Rated data	
Infeed power	
Rated value	55 kW (60 hp)
for S6 duty	71 kW
Maximum <sup>6)</sup>	91 kW
Regenerative feedback power	
Rated value	55 kW (60 hp)
for S6 duty	71 kW
Maximum <sup>7)</sup>	91 kW
DC-link current	
at 600 V DC	92 A
for S6 duty	121 A
Maximum <sup>8)</sup>	152 A
Input current	
at 380 V AC 3-phase	88 A
at 400 V AC 3-phase	84 A
at 480 V AC 3-phase	70 A
at 400 V S6 duty	108 A
at 400 V, maximum <sup>9)</sup>	139 A
Current requirement at 24 V DC, maximum	1.9 A
Ampacity of the busbars	
for electronics power supply at 24 V DC	20 A
for DC-link connection	200 A
DC link capacitance	
of the Active Line Module	1,880 µF
of the drive system, maximum	20,000 µF

General technical specifications	
Sound pressure level	60 dB
Losses <sup>10)</sup>	0.95 kW

Ambient conditions	
Ambient temperature in operation	0 ... 40 °C (32 ... 104 °F)
Cooling air throughput	0.044 m <sup>3</sup> /s (1.554 ft <sup>3</sup> /s)
Installation altitude	1,000 m (3,280.84 ft)
Type of cooling <sup>11)</sup>	Internal air cooling
RI suppression	Active Line Module + Active Interface Module: Category C3 according to EN 61800-3 up to 350 m (1148 ft) total cable length. With line filter: Category C2 according to EN 61800-3 up to 350 m (1148 ft) total cable length. Category C3 according to EN 61800-3 from 350 m to 1000 m (1148 ... 3281 ft) total cable length.

Standards	
Compliance with standards	CE, cULus

## Data sheet for Active Line Modules

Article No. : **6SL3130-7TE25-5AA3**

- <sup>1)</sup> in conjunction with the recommended Class J fuse, or circuit breaker according to UL489 / CSA 22.2 No. 5-02
- <sup>2)</sup> Factory setting can be altered by inputting a reactive current setpoint (Active Mode)
- <sup>3)</sup> In Active Mode, the DC link voltage is regulated and can be adjusted as a voltage decoupled from the line voltage. In Smart Mode, the DC link voltage is kept in proportion to the line voltage at the mean rectified line voltage value. For line voltages of 416 ... 480 V AC, Active Mode can also be selected if the connected motors are suitable for > 650 V DC.
- <sup>6)</sup> Higher peak output is possible in combination with the Active Interface Module 6SL3100-0BE25-5AB0 (110 kW).
- <sup>7)</sup> Higher peak output is possible in combination with the Active Interface Module 6SL3100-0BE25-5AB0 (110 kW).
- <sup>8)</sup> Higher peak output is possible in combination with the Active Interface Module 6SL3100-0BE25-5AB0 (176 A).
- <sup>9)</sup> Higher peak output is possible in combination with the Active Interface Module 6SL3100-0BE25-5AB0 (168 A).
- <sup>10)</sup> Power loss of the Active Line Module with rated power including losses of the 24 V DC electronics power supply
- <sup>11)</sup> Power units with intensified air cooling thanks to integrated fan