

Article No. : 6SL3130-7TE23-6AA3

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Figure similar



Electrical data	
Input	
Number of phases	3 AC
Line voltage	342 ... 528 V
Line frequency	47 ... 63 Hz
Short-circuit strength ¹⁾	65 kA
Line power factor	
in Active mode	
Fundamental power factor cos phi _{1 2)}	1
Total	1
in Smart Mode	
Fundamental power factor, minimal	.96
Total	0.65 ... 0.90
Overvoltage category	Class III
DC link voltage ³⁾	
at 380 V ... 400 V AC, factory setting	600 V
at 400 V ... 415 V AC, factory setting	625 V
DC-link voltage	1.35 x line voltage (Smart Mode)
Electronics power supply with DC	24 V (-15 % / 20 %)

Connections	
Line side	
Design	M6 bolt (X1)
Conductor cross-section	2.50 ... 50.00 mm ² (AWG 14 ... AWG 1)
PE conductor	M6 screw
Line length, max.	
Shielded ⁴⁾	630 m (2,066.93 ft)
Unshielded	850 m (2,788.71 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	10.0 kg (22.05 lb)
Dimensions	
Width	150 mm (5.91 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Rated data	
Infeed power	
Rated value	36 kW (40 hp)
for S6 duty	47 kW
Maximum	70 kW
Regenerative feedback power	
Rated value	36 kW (40 hp)
for S6 duty	47 kW
Maximum	70 kW
DC-link current	
at 600 V DC	60 A
for S6 duty	79 A
Maximum	117 A
Input current	
at 380 V AC 3-phase	58 A
at 400 V AC 3-phase	55 A
at 480 V AC 3-phase	46 A
at 400 V S6 duty	71 A
at 400 V, maximum	107 A
Current requirement at 24 V DC, maximum	1.5 A
Ampacity of the busbars	
for electronics power supply at 24 V DC	20 A
for DC-link connection	200 A
DC link capacitance	
of the Active Line Module	1,410 µF
of the drive system, maximum	20,000 µF

General technical specifications	
Sound pressure level	65 dB
Losses ¹⁰⁾	0.67 kW

Ambient conditions	
Ambient temperature in operation	0 ... 40 °C (32 ... 104 °F)
Cooling air throughput	0.031 m³/s (1.095 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Type of cooling ¹¹⁾	Internal air cooling
RI suppression	Active Line Module + Active Interface Module: Category C3 according to EN 61800-3 up to 350 m (1148 ft) total cable length. With line filter: Category C2 according to EN 61800-3 up to 350 m (1148 ft) total cable length. Category C3 according to EN 61800-3 from 350 m to 1000 m (1148 ... 3281 ft) total cable length.

Standards	
Compliance with standards	CE, cULus

Data sheet for Active Line Modules

Article No. : 6SL3130-7TE23-6AA3

¹⁾ in conjunction with the recommended Class J fuse, or circuit breaker according to UL489 / CSA 22.2 No. 5-02

²⁾ Factory setting can be altered by inputting a reactive current setpoint (Active Mode)

³⁾ In Active Mode, the DC link voltage is regulated and can be adjusted as a voltage decoupled from the line voltage. In Smart Mode, the DC link voltage is kept in proportion to the line voltage at the mean rectified line voltage value. For line voltages of 416 ... 480 V AC, Active Mode can also be selected if the connected motors are suitable for > 650 V DC.

⁴⁾ Max. cable lengths in conjunction with Active Interface Module and Basic Line Filter (Category C3 in accordance with EN 61800-3).

¹⁰⁾ Power loss of the Active Line Module with rated power including losses of the 24 V DC electronics power supply

¹¹⁾ Power units with intensified air cooling thanks to integrated fan