



Figure similar

Data sheet for terminal module

Article No. : 6SL3055-0AA00-3KA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

General technical specifications	
Power requirement (DC 24 V)	0.50 A
Power requirement for protection, max.	20 A
Power supply voltage	24 V
Conductor cross-section, on the line side	2.5 mm² (AWG 14)
PE conductor version	M4 screw
Power loss, max.	2.4 W

Relay outputs	
Number of DRIVE-CLiQ interfaces	2

Sensor inputs	
Number of sensor inputs <sup>9)</sup>	4
Conductor cross-section	0.2 ... 6 mm² (AWG 24 ... 10)
Constant current per sensor	2 mA
Voltage for protective separation with AC, max.	480 V

Mechanical data	
Net weight	0.41 kg (0.90 lb)
Dimensions	
Width	30 mm (1.18 in)
Height	150 mm (5.91 in)
Depth	111 mm (4.37 in)

<sup>9)</sup> 4 temperature sensor inputs for KTY84-130, PT1000 or PTC (Pt1000 can be used from firmware V4.7 HF17)