



Figure similar

MLFB-Ordering data 6SL3100-0BE25-5AB0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

| Electrical data | | General tech. specifications | |
|---|---------------------|------------------------------|------------------------|
| Input | | Sound pressure level | 66 dB |
| Number of phases | 3 AC | Power loss | 0.38 kW |
| Line voltage | 380 ... 480 V | Ambient conditions | |
| Internal resistor | 1440 Ω +10% -10% | Type of cooling | Internal air cooling |
| Rated data | | Cooling air throughput | 0.08 m³/s (2.93 ft³/s) |
| Rated current | 88 A | Standards | |
| Power requirement (DC 24 V) | 0.60 A | Compliance with standards | cURus |
| Switching current (as NC circuit at 250 V AC) | 1.6 A | Connections | |
| Switching current (as NC circuit at 60 V DC) | 0.75 A | Line side | |
| Mechanical data | | Version | screw-type terminal |
| Dimensions | | Conductor cross-section | 50 mm² (1 AWG) |
| Width | 200 mm (7.87 in) | PE conductor | M6 screw |
| Height | 380 mm (14.96 in) | | |
| Depth | 270 mm (10.63 in) | | |
| Degree of protection | IP20 / UL open type | | |
| Net weight | 23.20 kg (51.15 lb) | | |
| Type of construction | Booksize | | |