

SIEMENS

Data sheet for S120 Active Interface Module Booksize

MLFB-Ordering data

6SL3100-0BE28-0AB0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data		General tech. specifications	
Input		Sound pressure level	68 dB
Number of phases	3 AC	Power loss	0.49 kW
Line voltage	380 ... 480 V	Ambient conditions	
Internal resistor	1440 Ω +10% -10%	Type of cooling	Internal air cooling
Rated data		Cooling air throughput	0.17 m³/s (5.90 ft³/s)
Rated current	128 A	Standards	
Power requirement (DC 24 V)	1.20 A	Compliance with standards	cURus
Switching current (as NC circuit at 250 V AC)	1.6 A	Connections	
Switching current (as NC circuit at 60 V DC)	0.75 A	Line side	
Mechanical data		Version	M8 bolt
Dimensions		Conductor cross-section	2.5 mm² ... 120 mm² (14 ... -3 AWG) (Alternatively 2 x 50 mm²)
Width	300 mm (11.81 in)	PE conductor	M8 Screw
Height	380 mm (14.96 in)		
Depth	270 mm (10.63 in)		
Degree of protection	IP20 / UL open type		
Net weight	31.90 kg (70.33 lb)		
Type of construction	Booksize		