



Figure similar

MLFB-Ordering data 6SL3100-0BE21-6AB0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data		General tech. specifications	
Input		Sound pressure level	57 dB
Number of phases	3 AC	Power loss	0.27 kW
Line voltage	380 ... 480 V	Ambient conditions	
Internal resistor	1440 Ω +10% -10%	Type of cooling	Internal air cooling
Rated data		Cooling air throughput	0.03 m³/s (1.06 ft³/s)
Rated current	26 A	Standards	
Power requirement (DC 24 V)	0.25 A	Compliance with standards	cURus
Switching current (as NC circuit at 250 V AC)	1.6 A	Connections	
Switching current (as NC circuit at 60 V DC)	0.75 A	Line side	
Mechanical data		Version	connector
Dimensions		Conductor cross-section	16 mm² (6 AWG)
Width	100 mm (3.94 in)	PE conductor	M5 screw
Height	380 mm (14.96 in)		
Depth	270 mm (10.63 in)		
Degree of protection	IP20 / UL open type		
Net weight	11.60 kg (25.57 lb)		
Type of construction	Booksize		