



Figure similar

Data sheet for Smart Line Modules Booksize

Article No. : 6SL130-6TE21-6AA4

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Electrical data	
Input	
Number of phases	3 AC
Line voltage	342 ... 528 V
Line frequency	47 ... 63 Hz
Short-circuit strength <sup>1)</sup>	65 kA
Line power factor	
Fundamental power factor, minimal	.96
Total	0.65 ... 0.90
Overvoltage category	Class III
DC link voltage <sup>2)</sup>	
DC-link voltage	1.35 × line voltage
Electronics power supply with DC	24 V (-15 % / 20 %)

Connections	
Line side	
Design	screw-type terminal (X1)
Conductor cross-section	2.5 ... 10 mm² (AWG 14 ... AWG 8)
PE conductor	M5 screw
Shield connecting kit	Cable shield connection plate integrated into the connector
Line length, max.	
Shielded	630 m (2,066.93 ft)
Unshielded	850 m (2,788.71 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	7.0 kg (15.43 lb)
Dimensions	
Width	100 mm (3.94 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Standards	
Compliance with standards	CE, cULus

Rated data	
Infeed power	
Rated value	16.0 kW (18.0 hp)
for S6 duty	21.0 kW
Maximum	35.0 kW
Regenerative feedback power	
Rated value	16.0 kW (18.0 hp)
for S6 duty	21.0 kW
Maximum	35.0 kW
DC-link current	
at 540 V DC	30.0 A
at 600 V DC	27.0 A
for S6 duty	35.0 A
Maximum	59.0 A
Input current	
at 380 V AC 3-phase	29.0 A
at 400 V AC 3-phase	27.5 A
at 480 V AC 3-phase	24.5 A
at 400 V S6 duty	35.0 A
at 400 V, maximum	57.5 A
Current requirement at 24 V DC, maximum	0.95 A
Ampacity of the busbars	
for electronics power supply at 24 V DC	20 A
for DC-link connection	100 A
DC link capacitance	
of the Smart Line Module	710 µF
of the drive system, maximum	20,000 µF

General technical specifications	
Sound pressure level	60 dB
Losses <sup>4)</sup>	0.190 kW

Ambient conditions	
Ambient temperature in operation	0 ... 40 °C (32 ... 104 °F)
Cooling air throughput	0.016 m³/s (0.565 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Type of cooling	Internal air cooling
RI suppression	Standard: No radio interference suppression; With line filter: Category C2 to EN 61800-3 Total cable length up to 350 m (1148 ft) (shielded)

<sup>1)</sup>in conjunction with the recommended Class J fuse, or circuit breaker according to UL489 / CSA 22.2 No. 5-02  
<sup>2)</sup>The DC link voltage is maintained at the mean value of the rectified line voltage.  
<sup>4)</sup>Power loss of the Smart Line Module with rated power including losses of the 24 V DC electronics power supply