SIEMENS

## Data sheet for SINAMICS G120C

**Article No. :** **6SL3210-1KE15-8AB2**



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

### Rated data

| | | |
|---|---|---|
| **Input** | | |
| Number of phases | 3 AC | |
| Line voltage | 380 ... 480 V +10 % -20 % | |
| Line frequency | 47 ... 63 Hz | |
| Rated current (LO) | 7.40 A | |
| Rated current (HO) | 6.00 A | |
| **Output** | | |
| Number of phases | 3 AC | |
| **Rated voltage** | **400V IEC** | **480V NEC [1)]** |
| Rated power (LO) | 2.20 kW | 3.00 hp |
| Rated power (HO) | 1.50 kW | 2.00 hp |
| Rated current (LO) | 5.60 A | |
| Rated current (HO) | 4.10 A | |
| Rated current (IN) | 5.80 A | |
| Max. output current | 8.20 A | |
| Pulse frequency | 4 kHz | |
| Output frequency for vector control | 0 ... 240 Hz | |
| Output frequency for V/f control | 0 ... 550 Hz | |
| **Overload capability** | | |
| Low Overload (LO) | | |
| 150 % base load current IL for 3 s, followed by 110 % base load current IL for 57 s in a 300 s cycle time | | |
| High Overload (HO) | | |
| 200% base load current IH for 3 s, followed by 150% base load current IH for 57 s in a 300 s cycle time | | |

### General tech. specifications

| | |
|---|---|
| Power factor λ | 0.70 ... 0.85 |
| Offset factor cos φ | 0.95 |
| Efficiency η | 0.97 |
| Sound pressure level (1m) | 49 dB |
| Power loss | 76.4 W |
| Filter class (integrated) | Class A |

### Communication

| | |
|---|---|
| Communication | USS/MODBUS RTU |

### Inputs / outputs

| | |
|---|---|
| **Standard digital inputs** | |
| Number | 6 |
| Switching level: 0→1 | 11 V |
| Switching level: 1→0 | 5 V |
| Max. inrush current | 15 mA |
| **Fail-safe digital inputs** | |
| Number | 1 |
| **Digital outputs** | |
| Number as relay changeover contact | 1 |
| Output (resistive load) | DC 30 V, 0.5 A |
| Number as transistor | 1 |
| Output (resistive load) | DC 30 V, 0.5 A |
| **Analog / digital inputs** | |
| Number | 1 (Differential input) |
| Resolution | 10 bit |
| **Switching threshold as digital input** | |
| 0→1 | 4 V |
| 1→0 | 1.6 V |
| **Analog outputs** | |
| Number | 1 (Non-isolated output) |
| **PTC/ KTY interface** | |
| 1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C | |

### Closed-loop control techniques

| | |
|---|---|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC) | Yes |
| V/f ECO linear / square-law | Yes |
| Sensorless vector control | Yes |
| Vector control, with sensor | No |
| Encoderless torque control | No |
| Torque control, with encoder | No |

SIEMENS

## Data sheet for SINAMICS G120C

**Article No. :** **6SL3210-1KE15-8AB2**


| Ambient conditions | |
|---|---|
| Cooling | Air cooling using an integrated fan |
| Cooling air requirement | 0.005 m³/s (0.177 ft³/s) |
| Installation altitude | 1,000 m (3,280.84 ft) |
| **Ambient temperature** | |
| Operation | -10 ... 40 °C (14 ... 104 °F) |
| Transport | -40 ... 70 °C (-40 ... 158 °F) |
| Storage | -40 ... 70 °C (-40 ... 158 °F) |
| **Relative humidity** | |
| Max. operation | 95 % At 40 °C (104 °F), condensation and icing not permissible |

| Connections | |
|---|---|
| **Signal cable** | |
| Conductor cross-section | 0.15 ... 1.50 mm² (AWG 24 ... AWG 16) |
| **Line side** | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| **Motor end** | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| **DC link (for braking resistor)** | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| Line length, max. | 15 m (49.21 ft) |
| PE connection | On housing with M4 screw |
| **Max. motor cable length** | |
| Shielded | 50 m (164.04 ft) |
| Unshielded | 100 m (328.08 ft) |

| Mechanical data | |
|---|---|
| Degree of protection | IP20 / UL open type |
| Frame size | FSAA |
| Net weight | 1.40 kg (3.09 lb) |
| **Dimensions** | |
| Width | 73 mm (2.87 in) |
| Height | 173 mm (6.81 in) |
| Depth | 155 mm (6.10 in) |

| Standards | |
|---|---|
| Compliance with standards | UL, cUL, CE, C-Tick (RCM) |
| CE marking | EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC |

| Converter losses to IEC61800-9-2* | |
|---|---|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 29.3 % |




The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

[1] The output current and HP ratings are valid for the voltage range 440V-480V