

Article No. : 6SL3210-1PC22-8AL0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :


| Rated data  |                     |                        |
|---|---------------------|------------------------|
| Input   |                     |                        |
| Number of phases  | 3 AC                |                        |
| Line voltage  | 200 ... 240 V ±10 % |                        |
| Line frequency  | 47 ... 63 Hz        |                        |
| Rated current (LO)  | 37.00 A             |                        |
| Rated current (HO)  | 33.00 A             |                        |
| Output  |                     |                        |
| Number of phases  | 3 AC                |                        |
| Rated voltage   | 230V IEC            | 240V NEC <sup>1)</sup> |
| Rated power (LO)  | 7.50 kW             | 10.00 hp               |
| Rated power (HO)  | 5.50 kW             | 7.50 hp                |
| Rated current (LO)  | 28.00 A             |                        |
| Rated current (HO)  | 22.00 A             |                        |
| Max. output current   | 44.00 A             |                        |
| Pulse frequency   | 4 kHz               |                        |
| Output frequency for vector control   | 0 ... 200 Hz        |                        |
| Output frequency for V/f control  | 0 ... 550 Hz        |                        |
| Overload capability   |                     |                        |
| Low Overload (LO)   |                     |                        |
| 1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s<br>1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s   |                     |                        |
| High Overload (HO)  |                     |                        |
| 1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s<br>2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s |                     |                        |
| General tech. specifications  |                     |                        |
| Power factor λ  | 0.85                |                        |
| Offset factor cos φ   | 0.95                |                        |
| Efficiency η  | 0.97                |                        |
| Sound pressure level (1m)   | 65 dB               |                        |
| Power loss  | 0.26 kW             |                        |
| Filter class (integrated)   | Class A             |                        |

| Ambient conditions        |  |
|---------------------------|--|
| Cooling                   | Internal air cooling                     |
| Cooling air requirement   | 0.018 m³/s (0.653 ft³/s)                 |
| Installation altitude     | 1,000 m (3,280.84 ft)                    |
| Ambient temperature       |  |
| Operation LO              | -5 ... 40 °C (23 ... 104 °F)             |
| Operation HO              | -5 ... 50 °C (23 ... 122 °F)             |
| Transport                 | -25 ... 55 °C (-13 ... 131 °F)           |
| Storage                   | -25 ... 55 °C (-13 ... 131 °F)           |
| Relative humidity         |  |
| Max. operation            | 95 % RH, condensation not permitted      |
| Connections               |  |
| Line side                 |  |
| Version                   | Plug-in screw terminals                  |
| Conductor cross-section   | 6.00 ... 16.00 mm²<br>(AWG 10 ... AWG 6) |
| Motor end                 |  |
| Version                   | Plug-in screw terminals                  |
| Conductor cross-section   | 6.00 ... 16.00 mm²<br>(AWG 10 ... AWG 6) |
| Max. motor cable length   |  |
| Shielded                  | 50 m (164.04 ft)                         |
| Unshielded                | 100 m (328.08 ft)                        |
| Mechanical data           |  |
| Degree of protection      | IP20 / UL open type                      |
| Frame size                | FSC                                      |
| Net weight                | 5.20 kg (11.46 lb)                       |
| Dimensions                |  |
| Width                     | 140 mm (5.51 in)                         |
| Height                    | 355 mm (13.98 in)                        |
| Depth                     | 165 mm (6.50 in)                         |
| Standards                 |  |
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), SEMI F47      |
| CE marking                | Low-voltage directive 2006/95/EC         |

Data sheet for SINAMICS Power module PM240-2

Article No. : 6SL3210-1PC22-8AL0

| Converter losses to IEC61800-9-2*                    |         |
|--|---------|
| Efficiency class                                     | IE2     |
| Comparison with the reference converter (90% / 100%) | 45.90 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 220V-240V