SIEMENS

Error:
No CAD-Data available for this configuration.

# Data sheet for SINAMICS V20

## Article No. : 6SL3210-5BB21-1UV0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Figure similar

### Rated data

| | | |
|---|---|---|
| **Input** | | |
| Number of phases | 1 AC | |
| Line voltage | 200 ... 240 V -10 % +10 % | |
| Line frequency | 47 ... 63 Hz | |
| **Output** | | |
| Number of phases | 3 AC | |
| **Rated voltage** | **230V IEC** | **240V NEC [1]** |
| Rated power (LO) | 1.10 kW | 1.50 hp |
| Rated power (HO) | 1.10 kW | 1.50 hp |
| Rated current (LO) | 6.00 A | 6.00 A |
| Rated current (HO) | 6.00 A | 6.00 A |
| Rated current (IN) | 6.00 A | |
| Pulse frequency | 8.00 kHz | |
| Output frequency | 0 ... 550 Hz | |
| **Overload capability** | | |
| Low Overload (LO) | | |
| 110 % rated output current for 60 s, cycle time 300 s | | |
| High Overload (HO) | | |
| 150 % rated output current for 60 s, cycle time 300 s | | |

### General tech. specifications

| | |
|---|---|
| Power factor λ | 0.72 |
| Offset factor cos φ | 0.95 |
| Efficiency η | 0.98 |
| Filter class (integrated) | Unfiltered |

### Communication

| | |
|---|---|
| Communication | USS, Modbus RTU |

### Inputs / outputs

| | |
|---|---|
| **Standard digital inputs** | |
| Number | 4 |
| **Digital outputs** | |
| Number as relay changeover contact | 1 |
| Number as transistor | 1 |
| **Analog inputs** | |
| Number | 2 (Can be used as additional digital input) |
| **Analog outputs** | |
| Number | 1 |

### Ambient conditions

| | |
|---|---|
| Cooling | External fan |
| Installation altitude | 1,000 m (3,280.84 ft) |
| **Ambient temperature** | |
| Operation[2] | -10 ... 60 °C (14 ... 140 °F) |
| Storage | -40 ... 70 °C (-40 ... 158 °F) |
| **Relative humidity** | |
| Max. operation | 95 % |

### Connections

| | |
|---|---|
| **Max. motor cable length** | |
| Shielded | 25 m (82.02 ft) |
| Unshielded | 50 m (164.04 ft) |

### Mechanical data

| | |
|---|---|
| Mounting position | Through-hole mounting / wall mounting / side-by-side mounting |
| Degree of protection | IP20 / UL open type |
| Frame size | FSB |
| Net weight | 1.60 kg (3.53 lb) |
| **Dimensions** | |
| Width | 140.0 mm (5.51 in) |
| Height | 160.0 mm (6.30 in) |
| Depth | 164.5 mm (6.48 in) |

### Standards

| | |
|---|---|
| Compliance with standards | CE, cULus, C-Tick (RCM), KC |
| CE marking | EN 61800-5-1 /EN 60204-1 and EN 61800-3 |

[1] The output current and HP ratings are valid for the voltage range 220V-240V

[2] Please observe derating at temperatures of 40 °C or above