

Article No. : 6SL3210-5BE31-5UV0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Rated data

| Input              |                           |                        |
|--------------------|---------------------------|------------------------|
| Number of phases   | 3 AC                      |                        |
| Line voltage       | 380 ... 480 V -15 % +10 % |                        |
| Line frequency     | 47 ... 63 Hz              |                        |
| Output             |                           |                        |
| Number of phases   | 3 AC                      |                        |
| Rated voltage      | 400V IEC                  | 480V NEC <sup>1)</sup> |
| Rated power (LO)   | 15.00 kW                  | 20.00 hp               |
| Rated power (HO)   | 15.00 kW                  | 20.00 hp               |
| Rated current (LO) | 31.00 A                   | 31.00 A                |
| Rated current (HO) | 31.00 A                   | 31.00 A                |
| Rated current (IN) | 31.00 A                   |                        |
| Pulse frequency    | 4.00 kHz                  |                        |
| Output frequency   | 0 ... 550 Hz              |                        |

|                                                       |  |
|-------------------------------------------------------|--|
| Overload capability                                   |  |
| Low Overload (LO)                                     |  |
| 110 % rated output current for 60 s, cycle time 300 s |  |
| High Overload (HO)                                    |  |
| 150 % rated output current for 60 s, cycle time 300 s |  |

|                              |            |
|------------------------------|------------|
| General tech. specifications |            |
| Power factor λ               | 0.72       |
| Offset factor cos φ          | 0.95       |
| Efficiency η                 | 0.98       |
| Filter class (integrated)    | Unfiltered |

|               |                 |
|---------------|-----------------|
| Communication |                 |
| Communication | USS, Modbus RTU |

|                                    |                                             |
|------------------------------------|---------------------------------------------|
| Inputs / outputs                   |                                             |
| Standard digital inputs            |                                             |
| Number                             | 4                                           |
| Digital outputs                    |                                             |
| Number as relay changeover contact | 1                                           |
| Number as transistor               | 1                                           |
| Analog inputs                      |                                             |
| Number                             | 2 (Can be used as additional digital input) |
| Analog outputs                     |                                             |
| Number                             | 1                                           |

Ambient conditions

|                         |                                |
|-------------------------|--------------------------------|
| Cooling                 | External fan                   |
| Installation altitude   | 1,000 m (3,280.84 ft)          |
| Ambient temperature     |                                |
| Operation <sup>2)</sup> | -10 ... 60 °C (14 ... 140 °F)  |
| Storage                 | -40 ... 70 °C (-40 ... 158 °F) |
| Relative humidity       |                                |
| Max. operation          | 95 %                           |

Connections

|                         |                  |
|-------------------------|------------------|
| Max. motor cable length |                  |
| Shielded                | 25 m (82.02 ft)  |
| Unshielded              | 50 m (164.04 ft) |

Mechanical data

|                      |                                                               |
|----------------------|---------------------------------------------------------------|
| Mounting position    | Through-hole mounting / wall mounting / side-by-side mounting |
| Degree of protection | IP20 / UL open type                                           |
| Frame size           | FSD                                                           |
| Net weight           | 3.90 kg (8.60 lb)                                             |

|            |                    |
|------------|--------------------|
| Dimensions |                    |
| Width      | 240.0 mm (9.45 in) |
| Height     | 206.5 mm (8.13 in) |
| Depth      | 172.5 mm (6.79 in) |


Standards

|                           |                                         |
|---------------------------|-----------------------------------------|
| Compliance with standards | CE, cULus, C-Tick (RCM), KC             |
| CE marking                | EN 61800-5-1 /EN 60204-1 and EN 61800-3 |

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE31-5UV0

| Converter losses to IEC61800-9-2 *                   |        |
|------------------------------------------------------|--------|
| Efficiency class                                     | IE2    |
| Comparison with the reference converter (90% / 100%) | 37.6 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V

<sup>2)</sup>Please observe derating at temperatures of 40 °C or above