



Figure similar

MLFB-Ordering data 6SL3211-0AB23-0AA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		Ambient conditions	
Input		Installation altitude	1000 m
Number of phases	1 AC	Ambient temperature	
Line voltage	200 ... 240 V ±10 %	Operation	-10 ... 40 °C
Line frequency	47 ... 63 Hz	Storage	-40 ... 70 °C
Rated current	35.60 A	Relative humidity	
Output		Max. operation	95 % condensation not permitted
Number of phases	3 AC	Closed-loop control techniques	
Rated power	3.00 kW	V/f linear / square-law / parameterizable	Yes
Rated current (IN)	13.60 A	Standards	
Pulse frequency	8 kHz	Compliance with standards	UL, cUL, CE, C-Tick (RCM)
Output frequency for V/f control	0 ... 650 Hz	CE marking	Low-voltage directive 2006/95/EC
As a result of legal stipulations, a limit to 550 Hz is in production		Inputs / outputs	
General tech. specifications		Digital inputs	
Offset factor cos φ	0.95	Number	3
Communication		Analog inputs	
Communication	RS485	Number	1 (Analog variant, for setpoint (0...10 V, can be scaled or used as 4th digital input))
Mechanical data		Digital outputs	
Degree of protection	IP20 / UL open type	Number	1 (Isolated optocoupler output, NPN type)
Frame size	FSC		
Net weight	2.20 kg		
Width	184.0 mm		
Height	181.0 mm		
Depth	152.0 mm		