



Figure similar

MLFB-Ordering data 6SL3210-5HB10-2UF0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Communication	
Input		Communication	PROFINET
Number of phases	1 AC	Ambient conditions	
Line voltage	200 ... 240 V ±10 %	Installation altitude	1000 m (3280.84 ft)
Line frequency	45 ... 66 Hz	Cooling	convection cooling
Rated current	2.7 A	Ambient temperature during	
Inrush current	8.0 A	Operation	0 ... 50 °C (32 ... 122 °F)
Output			Better than class 3K3, in acc. with EN 60721-3-3: 2002, without derating
Number of phases	3 AC	Transport	-40 ... 70 °C (-40 ... 158 °F)
Rated power	0.20 kW		Class 2K4, in acc. with EN 60721-3-2: 1997, in transport packaging
Rated current I _N	1.4 A	Storage	-25 ... 55 °C (-13 ... 131 °F)
Max. output current	4.8 A		Class 1K4, in acc. with EN 60721-3-1: 1997, in product packaging
Pulse frequency	8 kHz	Relative humidity during	
Output frequency for servo control	0 ... 550 Hz	Max. operation	95 %
Electronics power supply			RH, condensation not permitted
Voltage	24 V -15 % ... +20 %	Transport, max.	95 %
Current demand, max.	0.8 A		at 40 °C (104 °F)
		Bearing, max.	95 %



MLFB-Ordering data

6SL3210-5HB10-2UF0

Inputs / outputs		Connections	
Standard digital inputs		Line side	
Number	5 of which 2 for F-DI	Version	push-in spring-type terminals
		Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG
Fail-safe digital inputs		Motor end	
Number	1 Can only be used for STO/SS1	Version	push-in spring-type terminals
		Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG
Mechanical data		DC link (for braking resistor)	
Dimensions		Version	push-in spring-type terminals
Width	45.0 mm (1.77 in)	Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG
Height without shield plate	170.0 mm (6.69 in)	Cable length	3 m (9.84 ft)
Depth	172.4 mm (6.79 in)	PE connection	
Mounting position	vertical wall mounting	Version	M4 screw studs
Degree of protection	IP20 / UL open type	Max. motor cable length ¹⁾	
Frame size	FSA	Shielded	50 m (164.04 ft)
Net weight	1.10 kg (2.43 lb)	Standards	
		Compliance with standards	CE, cULus, RCM, KC, EAC, UKCA
		CE marking	Low-voltage directive 2006/95/EC
		Verification of suitability for fail-safety	SIL 2 in acc. with IEC 61508 parts 1-3 (2010) and IEC 61800-5-2 (2016), PL d in acc. with ISO 13849 part 1 (2015), Category 3 in acc. with ISO 13849 part 1 (2015)

¹⁾ Cable length with possibility of connection an external filter