

## Data sheet for SINAMICS Power module PM240

Article No. : 6SL3224-0BE24-0UA0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

<b>Input</b>	
Number of phases	3 AC
Line voltage	380 ... 480 V ±10 %
Line frequency	47 ... 63 Hz
Rated current with line reactor	10.40 A
Rated current without line reactor	13.40 A

<b>Output</b>	
Number of phases	3 AC
<b>Rated voltage</b>	<b>400V IEC      480V NEC <sup>1)</sup></b>
Rated power (LO)	4.00 kW      5.00 hp
Rated power (HO)	4.00 kW      5.00 hp
Rated current (LO)	10.20 A
Rated current (HO)	10.20 A
Max. output current	20.40 A
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

<b>Overload capability</b>	
Low Overload (LO)	
1.1 × rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s	
High Overload (HO)	
1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s	

### General tech. specifications

Power factor λ	0.85
Offset factor cos φ	0.95
Efficiency η	0.95
Sound pressure level (1m)	50 dB
Power loss	0.18 kW
Filter class (integrated)	-

### Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.024 m³/s (0.848 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation LO	0 ... 40 °C (32 ... 104 °F)
Operation HO	0 ... 50 °C (32 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

<b>Relative humidity</b>	
Max. operation	95 % RH, condensation not permitted

### Connections

<b>Line side</b>	
Version	screw-type terminal
Conductor cross-section	1.00 ... 6.00 mm² (AWG 18 ... AWG 10)

<b>Motor end</b>	
Version	Screw-type terminals
Conductor cross-section	1.00 ... 6.00 mm² (AWG 18 ... AWG 10)

<b>DC link (for braking resistor)</b>	
Version	Screw-type terminals
Conductor cross-section	1.00 ... 6.00 mm² (AWG 18 ... AWG 10)
PE connection	On housing with M5 screw

<b>Max. motor cable length</b>	
Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

### Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSB
Net weight	4.00 kg (8.82 lb)
<b>Dimensions</b>	
Width	153 mm (6.02 in)
Height	270 mm (10.63 in)
Depth	165 mm (6.50 in)

### Standards

Compliance with standards	UL, cUL, CE, C-Tick (RCM), SEMI F47
CE marking	Low-voltage directive 2006/95/EC

## Data sheet for SINAMICS Power module PM240

Article No. : 6SL3224-0BE24-0UA0

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V