

Article No. : 6SL3224-0XE42-0UA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar


Rated data			
Input			
Number of phases		3 AC	
Line voltage		380 ... 480 V ±10 %	
Line frequency		47 ... 63 Hz	
Rated current with line reactor		354.00 A	
Rated current without line reactor		442.00 A	
Output			
Number of phases		3 AC	
Rated voltage		400V IEC	480V NEC ¹⁾
Rated power (LO)		250.00 kW	400.00 hp
Rated power (HO)		200.00 kW	300.00 hp
Rated current (LO)		477.00 A	
Rated current (HO)		370.00 A	
Max. output current		592.00 A	
Pulse frequency		2 kHz	
Output frequency for vector control		0 ... 200 Hz	
Output frequency for V/f control		0 ... 550 Hz	
Overload capability			
Low Overload (LO)			
1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s			
High Overload (HO)			
1.36 x output current rating (i.e., 136 % overload) for 57 s with a cycle time of 300 s 1.6 x output current rating (i.e., 160 % overload) for 3 s with a cycle time of 300 s			
General tech. specifications			
Power factor λ		0.85	
Offset factor cos φ		0.95	
Efficiency η		0.98	
Sound pressure level (1m)		69 dB	
Power loss		5.50 kW	
Filter class (integrated)		-	

Ambient conditions	
Cooling	Internal air cooling
Cooling air requirement	0.360 m³/s (12.713 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation LO	0 ... 40 °C (32 ... 104 °F)
Operation HO	0 ... 40 °C (32 ... 104 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)
Relative humidity	
Max. operation	95 % RH, condensation not permitted
Connections	
Line side	
Version	M10 bolt
Conductor cross-section	185.00 ... 240.00 mm² (AWG -5 ... MCM 500)
Motor end	
Version	M10 bolt
Conductor cross-section	185.00 ... 240.00 mm² (AWG -5 ... MCM 500)
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)
Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSGX
Net weight	174.00 kg (383.60 lb)
Dimensions	
Width	326 mm (12.83 in)
Height	1,533 mm (60.35 in)
Depth	547 mm (21.54 in)
Standards	
Compliance with standards	UL, cUL, CE, C-Tick (RCM), SEMI F47
CE marking	Low-voltage directive 2006/95/EC

Data sheet for SINAMICS Power module PM240

Article No. : 6SL3224-0XE42-0UA0

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	44.50 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V