

Article No. : 6SL3225-0BE37-5AA0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

<b>Input</b>	
Number of phases	3 AC
Line voltage	380 ... 480 V ±10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	166.00 A
Rated current (HO)	135.00 A

<b>Output</b>	
Number of phases	3 AC
<b>Rated voltage</b>	<b>400V IEC      480V NEC <sup>1)</sup></b>
Rated power (LO)	90.00 kW      125.00 hp
Rated power (HO)	75.00 kW      100.00 hp
Rated current (LO)	178.00 A
Rated current (HO)	145.00 A
Max. output current	290.00 A
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

<b>Overload capability</b>	
Low Overload (LO)	
1.1 × rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s	
High Overload (HO)	
1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s	

<b>General tech. specifications</b>	
Power factor λ	0.90
Offset factor cos φ	0.95
Efficiency η	0.97
Sound pressure level (1m)	65 dB
Power loss	2.31 kW
Filter class (integrated)	Class A

### Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.117 m³/s (4.132 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation LO	0 ... 40 °C (32 ... 104 °F)
Operation HO	0 ... 50 °C (32 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

<b>Relative humidity</b>	
Max. operation	95 % RH, condensation not permitted

### Connections

<b>Line side</b>	
Version	M8 bolt
Conductor cross-section	25.00 ... 120.00 mm² (AWG 4 ... AWG -3)
<b>Motor end</b>	
Version	M8 bolt
Conductor cross-section	25.00 ... 120.00 mm² (AWG 4 ... AWG -3)

<b>Max. motor cable length</b>	
Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

### Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSF
Net weight	51.00 kg (112.44 lb)
<b>Dimensions</b>	
Width	350 mm (13.78 in)
Height	934 mm (36.77 in)
Depth	316 mm (12.44 in)


### Standards

Compliance with standards	CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC

Data sheet for SINAMICS Power module PM250

Article No. : 6SL3225-0BE37-5AA0

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	54.08 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V