

Article No. : 6SL3223-0DE21-1BG1



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

<b>Input</b>	
Number of phases	3 AC
Line voltage	380 ... 480 V ±10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	3.20 A
Rated current (HO)	2.30 A

<b>Output</b>	
Number of phases	3 AC
<b>Rated voltage</b>	<b>400V IEC      480V NEC <sup>1)</sup></b>
Rated power (LO)	1.10 kW      1.50 hp
Rated power (HO)	0.75 kW      1.00 hp
Rated current (LO)	3.10 A
Rated current (HO)	2.20 A
Max. output current	4.70 A
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

<b>Overload capability</b>	
Low Overload (LO)	
1.1 × rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s	
High Overload (HO)	
1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s	

### General tech. specifications

Power factor λ	0.90
Offset factor cos φ	0.95
Efficiency η	0.94
Sound pressure level (1m)	62 dB
Power loss	0.07 kW
Filter class (integrated)	Class B

### Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.007 m³/s (0.247 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation LO	-10 ... 40 °C (14 ... 104 °F)
Operation HO	-10 ... 50 °C (14 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

<b>Relative humidity</b>	
Max. operation	95 % RH, condensation not permitted

### Connections

<b>Line side</b>	
Version	Plug-in screw terminals
Conductor cross-section	1.00 ... 2.50 mm² (AWG 18 ... AWG 14)
<b>Motor end</b>	
Version	Plug-in screw terminals
Conductor cross-section	1.00 ... 2.50 mm² (AWG 18 ... AWG 14)

<b>Max. motor cable length</b>	
Shielded	25 m (82.02 ft)
Unshielded	100 m (328.08 ft)

### Mechanical data

Degree of protection	IP55 / UL type 12
Frame size	FSA
Net weight	4.30 kg (9.48 lb)
<b>Dimensions</b>	
Width	154 mm (6.06 in)
Height	460 mm (18.11 in)
Depth	249 mm (9.80 in)


### Standards

Compliance with standards	UL, CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC

Data sheet for SINAMICS Power module PM230

Article No. : 6SL3223-0DE21-1BG1

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	29.80 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V