

Article No. : 6SL3223-0DE23-0AG1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

| | |
|--------------------|---------------------|
| Input | |
| Number of phases | 3 AC |
| Line voltage | 380 ... 480 V ±10 % |
| Line frequency | 47 ... 63 Hz |
| Rated current (LO) | 8.00 A |
| Rated current (HO) | 6.10 A |

| | |
|-------------------------------------|---|
| Output | |
| Number of phases | 3 AC |
| Rated voltage | 400V IEC 480V NEC ¹⁾ |
| Rated power (LO) | 3.00 kW 4.00 hp |
| Rated power (HO) | 2.20 kW 3.00 hp |
| Rated current (LO) | 7.70 A |
| Rated current (HO) | 5.90 A |
| Max. output current | 11.80 A |
| Pulse frequency | 4 kHz |
| Output frequency for vector control | 0 ... 200 Hz |
| Output frequency for V/f control | 0 ... 550 Hz |

| | |
|---|--|
| Overload capability | |
| Low Overload (LO) | |
| 1.1 × rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s | |
| High Overload (HO) | |
| 1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s | |

| | |
|-------------------------------------|---------|
| General tech. specifications | |
| Power factor λ | 0.90 |
| Offset factor cos φ | 0.95 |
| Efficiency η | 0.96 |
| Sound pressure level (1m) | 62 dB |
| Power loss | 0.12 kW |
| Filter class (integrated) | Class A |

Ambient conditions

| | |
|----------------------------|--------------------------------|
| Cooling | Internal air cooling |
| Cooling air requirement | 0.007 m³/s (0.247 ft³/s) |
| Installation altitude | 1,000 m (3,280.84 ft) |
| Ambient temperature | |
| Operation LO | -10 ... 40 °C (14 ... 104 °F) |
| Operation HO | -10 ... 50 °C (14 ... 122 °F) |
| Transport | -25 ... 55 °C (-13 ... 131 °F) |
| Storage | -25 ... 55 °C (-13 ... 131 °F) |

| | |
|--------------------------|-------------------------------------|
| Relative humidity | |
| Max. operation | 95 % RH, condensation not permitted |

Connections

| | |
|-------------------------|--|
| Line side | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| Motor end | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |

| | |
|--------------------------------|-------------------|
| Max. motor cable length | |
| Shielded | 50 m (164.04 ft) |
| Unshielded | 100 m (328.08 ft) |

Mechanical data

| | |
|----------------------|-------------------|
| Degree of protection | IP55 / UL type 12 |
| Frame size | FSA |
| Net weight | 4.30 kg (9.48 lb) |
| Dimensions | |
| Width | 154 mm (6.06 in) |
| Height | 460 mm (18.11 in) |
| Depth | 249 mm (9.80 in) |


Standards

| | |
|---------------------------|----------------------------------|
| Compliance with standards | UL, CE, C-Tick (RCM) |
| CE marking | Low-voltage directive 2006/95/EC |

Data sheet for SINAMICS Power module PM230

Article No. : 6SL3223-0DE23-0AG1

| Converter losses to IEC61800-9-2* | |
|--|---------|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 31.70 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V