

Article No. : 6SL3223-0DE31-5AG1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input			
Number of phases	3 AC		
Line voltage	380 ... 480 V ±10 %		
Line frequency	47 ... 63 Hz		
Rated current (LO)	33.00 A		
Rated current (HO)	27.00 A		
Output			
Number of phases	3 AC		
Rated voltage	400V IEC	480V NEC ¹⁾	
Rated power (LO)	15.00 kW	20.00 hp	
Rated power (HO)	11.00 kW	15.00 hp	
Rated current (LO)	32.00 A		
Rated current (HO)	26.00 A		
Max. output current	52.00 A		
Pulse frequency	4 kHz		
Output frequency for vector control	0 ... 200 Hz		
Output frequency for V/f control	0 ... 550 Hz		

Overload capability

Low Overload (LO)
1.1 × rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s
High Overload (HO)
1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

General tech. specifications

Power factor λ	0.90
Offset factor cos φ	0.95
Efficiency η	0.97
Sound pressure level (1m)	66 dB
Power loss	0.39 kW
Filter class (integrated)	Class A

Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.020 m³/s (0.706 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation LO	-10 ... 40 °C (14 ... 104 °F)
Operation HO	-10 ... 50 °C (14 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------

Connections

Line side

Version	Plug-in screw terminals
Conductor cross-section	10.00 ... 16.00 mm² (AWG 8 ... AWG 6)

Motor end

Version	Plug-in screw terminals
Conductor cross-section	10.00 ... 16.00 mm² (AWG 8 ... AWG 6)

Max. motor cable length

Shielded	25 m (82.02 ft)
Unshielded	100 m (328.08 ft)

Mechanical data

Degree of protection	IP55 / UL type 12
Frame size	FSC
Net weight	9.50 kg (20.94 lb)

Dimensions

Width	230 mm (9.06 in)
Height	620 mm (24.41 in)
Depth	249 mm (9.80 in)


Standards

Compliance with standards	UL, CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC

Data sheet for SINAMICS Power module PM230

Article No. : 6SL3223-0DE31-5AG1

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	31.80 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V