

Data sheet for SINAMICS Control unit CU240E-2

Article No. : 6SL3244-0BB12-1BA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Electrical data	
Operating voltage via	
The Power Module	DC 24 V
External power supply	DC 20 ... 29 V
Max. power consumption	0.50 A
Power loss	5.50 W

Communication	
Communication	RS485

Inputs / outputs	
Standard digital inputs	
Number	6
Switching level: 0→1	11 V
Switching level: 1→0	5 V
Fail-safe digital inputs	
Number	1 (Use of 2 × DI Standard)
Digital outputs	
as relay changer	
Number	2
Analog / digital inputs	
Number	2 (Differential input)
Analog outputs	
Number	2 (Non-isolated output)

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	Yes
Torque control, with encoder	No

Ambient conditions	
Ambient temperature	
Operation	-10 ... 55 °C (14 ... 131 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)
Relative humidity	
Max. operation	95 %

Connections	
Signal cable	
Conductor cross-section	0.05 ... 1.50 mm² (AWG 28 ... AWG 16)

Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	0.49 kg (1.08 lb)
Dimensions	
Width	73.0 mm (2.87 in)
Height	199.0 mm (7.83 in)
Depth	46.0 mm (1.81 in)

Standards	
Compliance with standards	CE, UL, cUL, RCM, SEMI F47
CE marking	Low-voltage directive 2014/35/EC