

Data sheet for Braking Module

Article No. : 6SL3300-1AE32-5AA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Rated power P _{DB}	50.00 kW
Rated power, max.	250.00 kW
Activation threshold	774 V (673 V)
adjustable via DIP switch	

General technical specifications	
DC link voltage	DC 510 ... 720 V

Mechanical data	
Net weight	7.3 kg (16.09 lb)

Digital inputs	
Number	1
Voltage	24 V
Low level	-3 V ... 5 V
High level	15 V ... 30 V
Power consumption at 24 V DC, typ.	10 mA

Digital outputs	
Number	1
Voltage	DC 24 V
Load current per digital output, max.	500 mA

Connections	
-------------	--

Digital inputs	
Connection cross-section, max.	1.5 mm² (16 AWG)

Digital outputs	
Connection cross-section, max.	1.5 mm² (16 AWG)

PE connection	
Version on housing	M8 nut

BrakeResistor	
Connection cross-section, max.	50.0 mm² (1 AWG)