

Data sheet for Motor Module

Article No. : 6SL3320-1TG32-2AA3



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
DC link voltage	DC 675 ... 1,035 V
Electronics power supply	DC 24 V -15 % / +20 %
Current demand, max.	0.90 A
Current consumption 500V AC	1.50 A
Current consumption 690V AC	1.00 A
DC-link current	
Rated current I _N DC	
- Basic/Smart Line Module	258 A
- Active Line Module	232 A
Base-load current I _L DC	
- Basic/Smart Line Module	251 A
- Active Line Module	226 A
Base-load current I _H DC	
- Basic/Smart Line Module	229 A
- Active Line Module	206 A
Output current	
Rated value I _N	215 A
Base-load current I _L ¹⁾	208 A
Base load current I _H ²⁾	192 A
I _{max}	312 A
Type rating ³⁾	
Based on I _N	200 kW
Based on I _H	160 kW
Pulse frequency	
Rated pulse frequency ⁴⁾	1.25 kHz
Pulse frequency, max.	1.25 kHz
DC link capacitance	2,800 µF
Output frequency for servo control	0 ... 550 Hz
Output frequency for V/f control	0 ... 550 Hz
Output frequency for vector control	0 ... 550 Hz
Ambient conditions	
Installation altitude (without derating)	2,000 m (6,561.68 ft)
Cooling ⁵⁾	air cooled
Cooling air requirement	0.36 m³/s (12.710 ft³/s)
Ambient temperature	
During operation	0 ... 40 °C (32 ... 104 °F)

Connections	
Motor end	
Version	2 x M10 screw
Conductor cross-section	2 x 240 mm²
DC link	
Version	2 x M10 screw
Conductor cross-section	2 x 240 mm²
Braking module	
Version	M6 bolt
PE1 connection	
Version	2 x M10 screw
Conductor cross-section	2 x 240 mm²
PE2 connection	
Version	2 x M10 screw
Conductor cross-section	2 x 240 mm²
Max. motor cable length ⁶⁾	
Shielded	300 m (984.25 ft)
Unshielded	450 m (1,476.38 ft)

Standards	
Compliance with standards	CE / C-Tick (RCM)
Safety Integrated	SIL 2 acc. to IEC 61508, PL d acc. to EN ISO 13849-1, Category 3 acc. to EN ISO 13849-1

Mechanical data	
Line side	
Dimensions	
Width	326 mm (12.83 in)
Height	1,533 mm (60.35 in)
Depth	545 mm (21.46 in)
Degree of protection	IP20
Type of construction	Chassis
Net weight	136 kg (299.83 lb)

General tech. specifications	
Sound pressure level (1m) + 50 Hz / 60 Hz	69 dB / 73 dB
At 50 Hz 690 V	3.09 kW
At 60 Hz 575 V	2.91 kW

¹⁾ The base-load current I_L is the basis for a duty cycle of 110% for 60 s or 150% for 10 s with a duty cycle duration of 300 s.
²⁾ The base load current I_H is based on a duty cycle of 150% for 60 s or 160% for 10 s with a duty cycle duration of 300 s.
³⁾ Rated power of a typical 6-pole standard induction motor based on I_L or I_H at 3 AC 50 Hz 500 V or 690 V, 3 AC 60 Hz 575 V.
⁴⁾ Information on the correlation between pulse frequency and maximum output current/output frequency is provided in the SINAMICS Low Voltage Configuration Manual.
⁵⁾ Power units with intensified air cooling thanks to integrated fan
⁶⁾ Sum of all motor cables and DC link. Longer cable lengths on request, depending on configuration. More information can be found in the SINAMICS Low Voltage Configuration Manual.