



SINAMICS S150

MLFB-Ordering data: 6SL3710-7LE41-0AA3

Client order no.:  
Order no.:  
Offer no.:  
Remarks:

Item no.:  
Consignment no.:  
Project:

Rated data:		Environmental conditions:	
Input:		Installation altitude	1000 m
Supply frequency	47...63 Hz	Coolant	Air
Supply voltage	400 V ±10%	Coolant requirement, air	2.60 m³/s
Rated input current	888 A	Min. ambient temperature	0 °C
Max. current	1477 A	Max. ambient temperature	40 °C
Pulse number	6		
Energy recovery capability	Yes (4Q)		
Output:		Special design:	
Output voltage	400 V		
Rated power (LO) in kW	560 kW		
Rated power (HO) in kW	450 kW		
Rated output current	985 A		
Rated output current (LO)	960 A		
Rated output current (HO)	860 A		
Output current Max	1440 A		
Pulse frequency (factory setting)	1.25 kHz		
Basic data:			
Efficiency $\eta$	96.00 %		
Power losses $\Delta P$	27.25 kW		
Power loss including options	27.25 kW		
Sound pressure level $L_{pA}$ (1 m)	77 dB		
Conductor cross section, max. (IEC)	8 x 240 mm²		
Degree of protection	IP20		
Width	2800 mm		
Height	2000 mm		
Depth	600 mm		
Weight approx.	2408 kg		
Frame size	J		
Color, paint shade	RAL7035		