



Data sheet for SINAMICS G150

MLFB-Ordering data: 6SL3710-1GE35-0AA3

Client order no.:
Order no.:
Offer no.:
Remarks:

Item no.:
Consignment no.:
Project:

Rated data	
Input	
Supply frequency	47...63 Hz
Supply voltage	400 V ±10%
Rated input current	509 A
Max. current	781 A
Pulse number	6
Energy recovery capability	No (2Q)
Output:	
Output voltage	400 V
Rated power (LO) in kW	250 kW
Rated power (HO) in kW	200 kW
Rated output current	490 A
Rated output current (LO)	477 A
Rated output current (HO)	438 A
Output current Max	715 A
Pulse frequency (factory setting)	2 kHz

Basic data:	
Power losses ΔP	6.56 kW
Power loss including options	6.56 kW
Sound pressure level L _{pA} (1 m)	69 dB
Conductor cross section, max. (IEC)	4 x 240 mm²
Degree of protection	IP20
Dimensions (W x H x D)	2000 mm x 1000 mm x 600 mm
Weight approx.	670 kg
Frame size	G
Design	A
Color, paint shade	RAL7035

Environmental conditions	
Installation altitude	1000 m
Coolant	Air
Coolant requirement, air	0.36 m³/s
Ambient temperature	0 °C - +40 °C

Converter losses to IEC61800-9-2*

Efficiency class IE2

Comparison with the reference converter (90% / 100%) 47.2 %

f (%)	I (%)	Power Loss (W)	Loss (%)
0	25	2130	0.60
0	50	2800	0.80
0	100	4860	1.40
50	25	2260	0.70
50	50	3080	0.90
50	100	5550	1.60
90	50	3440	1.00
90	100	6560	1.90

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter including line choke without options/components.

*calculated values

Special design
