



Figure similar

MLFB-Ordering data                      1FK7022-5AK21-1DA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                               | Mechanical data          |                                                                                                                            |
|-----------------------------|-------------------------------|--------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Rated speed (100 K)         | 6000 rpm                      | Motor type               | Permanent-magnet synchronous motor                                                                                         |
| Number of poles             | 6                             | Motor type               | Compact                                                                                                                    |
| Rated torque (100 K)        | 0.6 Nm                        | Shaft height             | 28                                                                                                                         |
| Rated current               | 1.4 A                         | Cooling                  | Natural cooling                                                                                                            |
| Static torque (60 K)        | 0.70 Nm                       | Radial runout tolerance  | 0.035 mm                                                                                                                   |
| Static torque (100 K)       | 0.85 Nm                       | Concentricity tolerance  | 0.08 mm                                                                                                                    |
| Stall current (60 K)        | 1.50 A                        | Axial runout tolerance   | 0.08 mm                                                                                                                    |
| Stall current (100 K)       | 1.80 A                        | Vibration severity grade | Grade A                                                                                                                    |
| Moment of inertia           | 0.280 kgcm²                   | Connector size           | 1                                                                                                                          |
| Efficiency                  | 86.0 %                        | Degree of protection     | IP64                                                                                                                       |
| Physical constants          |                               | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                                                                                       |
| Torque constant             | 0.46 Nm/A                     | Temperature monitoring   | Pt1000 temperature sensor                                                                                                  |
| Voltage constant at 20° C   | 29.0 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable                                                                                 |
| Winding resistance at 20° C | 4.20 Ω                        | Color of the housing     | without                                                                                                                    |
| Rotating field inductance   | 9.1 mH                        | Holding brake            | without holding brake                                                                                                      |
| Electrical time constant    | 2.20 ms                       | Shaft end                | Feather key                                                                                                                |
| Mechanical time constant    | 1.70 ms                       | Encoder system           | Encoder IC22DQ: incremental encoder 22 bits (resolution 4194304, encoder-internal 2048 S/R) + commutation position 11 bits |
| Thermal time constant       | 18 min                        |                          |                                                                                                                            |
| Shaft torsional stiffness   | 3000 Nm/rad                   |                          |                                                                                                                            |
| Net weight of the motor     | 1.8 kg                        |                          |                                                                                                                            |



Figure similar

MLFB-Ordering data                      1FK7022-5AK21-1DA0

| Optimum operating point           |           | Recommended Motor Module |         |
|-----------------------------------|-----------|--------------------------|---------|
| Optimum speed                     | 6000 rpm  | Rated inverter current   | 2 A     |
| Optimum power                     | 0.4 kW    | Maximum inverter current | 5 A     |
| Limiting data                     |           | Maximum torque           | 2.00 Nm |
| Max. permissible speed (mech.)    | 10000 rpm |                          |         |
| Max. permissible speed (inverter) | 9990 rpm  |                          |         |
| Maximum torque                    | 3.4 Nm    |                          |         |
| Maximum current                   | 8.0 A     |                          |         |