

Data sheet for SIMOTICS S-1FK7



MLFB-Ordering data                      1FK7032-2AK71-1PB0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                               | Mechanical data          |                                                                      |
|-----------------------------|-------------------------------|--------------------------|----------------------------------------------------------------------|
| Rated speed (100 K)         | 6000 rpm                      | Motor type               | Permanent-magnet synchronous motor                                   |
| Number of poles             | 6                             | Motor type               | Compact                                                              |
| Rated torque (100 K)        | 0.8 Nm                        | Shaft height             | 36                                                                   |
| Rated current               | 1.3 A                         | Cooling                  | Natural cooling                                                      |
| Static torque (60 K)        | 0.95 Nm                       | Radial runout tolerance  | 0.035 mm                                                             |
| Static torque (100 K)       | 1.10 Nm                       | Concentricity tolerance  | 0.08 mm                                                              |
| Stall current (60 K)        | 1.40 A                        | Axial runout tolerance   | 0.08 mm                                                              |
| Stall current (100 K)       | 1.70 A                        | Vibration severity grade | Grade A                                                              |
| Moment of inertia           | 0.750 kgcm²                   | Connector size           | 1                                                                    |
| Efficiency                  | 88.0 %                        | Degree of protection     | IP64                                                                 |
| Physical constants          |                               | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                                 |
| Torque constant             | 0.67 Nm/A                     | Temperature monitoring   | Pt1000 temperature sensor                                            |
| Voltage constant at 20° C   | 45.0 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable                           |
| Winding resistance at 20° C | 5.05 Ω                        | Color of the housing     | Standard (Anthracite RAL 7016)                                       |
| Rotating field inductance   | 17.3 mH                       | Holding brake            | with holding brake                                                   |
| Electrical time constant    | 3.45 ms                       | Shaft end                | Feather key                                                          |
| Mechanical time constant    | 2.20 ms                       | Encoder system           | Resolver R14DQ: resolver 14 bits (resolution 16384, internal 2-pole) |
| Thermal time constant       | 25 min                        |                          |                                                                      |
| Shaft torsional stiffness   | 4100 Nm/rad                   |                          |                                                                      |
| Net weight of the motor     | 3.1 kg                        |                          |                                                                      |



Figure similar

MLFB-Ordering data                    1FK7032-2AK71-1PB0

| Optimum operating point           |                        | Recommended Motor Module |         |
|-----------------------------------|------------------------|--------------------------|---------|
| Optimum speed                     | 6000 rpm               | Rated inverter current   | 3 A     |
| Optimum power                     | 0.5 kW                 | Maximum inverter current | 9 A     |
| Limiting data                     |                        | Maximum torque           | 4.50 Nm |
| Max. permissible speed (mech.)    | 10000 rpm              |                          |         |
| Max. permissible speed (inverter) | 10000 rpm              |                          |         |
| Maximum torque                    | 4.5 Nm                 |                          |         |
| Maximum current                   | 7.0 A                  |                          |         |
| Holding brake                     |                        |                          |         |
| Holding brake version             | Permanent-magnet brake |                          |         |
| Holding torque                    | 1.9 Nm                 |                          |         |
| Power supply voltage              | DC 24 V ± 10 %         |                          |         |
| Coil current                      | 0.3 A                  |                          |         |
| Opening time                      | 50 ms                  |                          |         |
| Closing time                      | 30 ms                  |                          |         |
| Highest braking work              | 40 J                   |                          |         |