



图像类似 / Figure similar

客户订单号 / Client order no.:
西门子订单号 / Order no.:
报价号 / Offer no.:
注释 / Remarks:

物品号 / Item no.:
托运号 / Consignment no.:
项目 / Project:

选型数据 / Engineering data		机械数据 / Mechanical data	
额定转速 (100 K) <i>Rated speed (100 K)</i>	6000 rpm	电机类型 <i>Motor type</i>	永磁同步电机 <i>Permanent-magnet synchronous motor</i>
极数 <i>Number of poles</i>	6	电机类型 <i>Motor type</i>	Compact
额定扭矩 (100 K) <i>Rated torque (100 K)</i>	1.0 Nm	轴高 <i>Shaft height</i>	36
额定电流 <i>Rated current</i>	1.3 A	冷却 <i>Cooling</i>	自冷却 <i>Natural cooling</i>
静态扭矩 (60 K) <i>Static torque (60 K)</i>	1.35 Nm	圆跳公差 <i>Radial runout tolerance</i>	0.035 mm
静态扭矩 (100 K) <i>Static torque (100 K)</i>	1.60 Nm	同轴度公差 <i>Concentricity tolerance</i>	0.08 mm
静止电流 (60 K) <i>Stall current (60 K)</i>	1.55 A	端面跳动公差 <i>Axial runout tolerance</i>	0.08 mm
静止电流 (100 K) <i>Stall current (100 K)</i>	1.90 A	振动值等级 <i>Vibration severity grade</i>	等级 A <i>Grade A</i>
转动惯量 <i>Moment of inertia</i>	1.000 kgcm²	连接器尺寸 <i>Connector size</i>	1
有效系数 <i>Efficiency</i>	88.0 %	防护等级 <i>Degree of protection</i>	IP64 <i>IP64</i>
物理常量 / Physical constants		结构型式, 根据代码 I <i>Design acc. to Code I</i>	IM B5 (IM V1,IM V3)
扭矩常量 <i>Torque constant</i>	0.84 Nm/A	温度监视 <i>Temperature monitoring</i>	温度传感器 Pt1000 <i>Pt1000 temperature sensor</i>
电压常数, 20° C 时 <i>Voltage constant at 20° C</i>	55.0 V/1000*min ⁻¹	电子连接的排列 <i>Electrical connectors</i>	信号和功率的插头, 可旋转 <i>Connectors for signals and power rotatable</i>
绕组电阻, 20° C 时 <i>Winding resistance at 20° C</i>	4.46 Ω	外壳的特殊颜色 <i>Color of the housing</i>	标准 (煤灰色 RAL 7016) <i>Standard (Anthracite RAL 7016)</i>
旋转电感 <i>Rotating field inductance</i>	17.2 mH	抱闸 <i>Holding brake</i>	带抱闸 <i>with holding brake</i>
电气时间常数 <i>Electrical time constant</i>	3.85 ms	轴端 <i>Shaft end</i>	光轴 <i>Plain shaft</i>
机械时间常数 <i>Mechanical time constant</i>	1.71 ms	编码器系统 <i>Encoder system</i>	多极旋转变压器 (极对数与电机的极对数一致) <i>Multi-pole resolver (number of pole pairs corresponds to number of pole pairs of the motor)</i>
热时间常数 <i>Thermal time constant</i>	30 min		
轴抗扭刚度 <i>Shaft torsional stiffness</i>	3750 Nm/rad		
电机净重 <i>Net weight of the motor</i>	3.9 kg		



图像类似 / Figure similar

订购数据
MLFB-Ordering data

1FK7034-2AK74-1SH0

最佳工作点 / Optimum operating point		推荐的电机模块 / Recommended Motor Module	
最佳转速 <i>Optimum speed</i>	6000 rpm	变频器额定电流 <i>Rated inverter current</i>	3 A
最佳功率 <i>Optimum power</i>	0.6 kW	变频器最大电流 <i>Maximum inverter current</i>	9 A
极限数据 / Limiting data		最大扭矩 <i>Maximum torque</i>	6.50 Nm
最大允许转速（机械） <i>Max. permissible speed (mech.)</i>	10000 rpm		
最大允许转速（变频器） <i>Max. permissible speed (inverter)</i>	10000 rpm		
最大扭矩 <i>Maximum torque</i>	6.5 Nm		
最大电流 <i>Maximum current</i>	8.0 A		
抱闸 / Holding brake			
抱闸型号 <i>Holding brake version</i>	永磁抱闸 <i>Permanent-magnet brake</i>		
支撑力矩 <i>Holding torque</i>	1.9 Nm		
供电电压 <i>Power supply voltage</i>	DC 24 V ± 10 %		
线圈电流 <i>Coil current</i>	0.3 A		
开启时间 <i>Opening time</i>	50 ms		
闭合时间 <i>Closing time</i>	30 ms		
最高开关操作功 <i>Highest braking work</i>	40 J		