

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7084-3BC71-1QH1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data	
Rated speed (100 K)	2000 rpm
Number of poles	8
Rated torque (100 K)	15.0 Nm
Rated current	6.7 A
Static torque (60 K)	16.60 Nm
Static torque (100 K)	20.00 Nm
Stall current (60 K)	6.90 A
Stall current (100 K)	8.50 A
Moment of inertia	102.000 kgcm²
Efficiency	93.0 %
Physical constants	
Torque constant	2.36 Nm/A
Voltage constant at 20° C	152.0 V/1000*min ⁻¹
Winding resistance at 20° C	0.58 Ω
Rotating field inductance	12.0 mH
Electrical time constant	20.50 ms
Mechanical time constant	3.10 ms
Thermal time constant	55 min
Shaft torsional stiffness	62000 Nm/rad
Net weight of the motor	26.0 kg

Mechanical data	
Motor type	Permanent-magnet synchronous motor
Motor type	High Inertia
Shaft height	80
Cooling	Natural cooling
Radial runout tolerance	0.050 mm
Concentricity tolerance	0.10 mm
Axial runout tolerance	0.10 mm
Vibration severity grade	Grade A
Connector size	1
Degree of protection	IP65
Design acc. to Code I	IM B5 (IM V1, IM V3)
Temperature monitoring	Pt1000 temperature sensor
Electrical connectors	Connectors for signals and power rotatable
Color of the housing	Standard (Anthracite RAL 7016)
Holding brake	with holding brake
Shaft end	Plain shaft
Encoder system	Encoder AS20DQI: absolute encoder single-turn 20 bits



Figure similar

MLFB-Ordering data 1FK7084-3BC71-1QH1

Optimum operating point		Recommended Motor Module	
Optimum speed	2000 rpm	Rated inverter current	9 A
Optimum power	3.1 kW	Maximum inverter current	27 A
Limiting data		Maximum torque	58.40 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	3800 rpm		
Maximum torque	61.0 Nm		
Maximum current	28.5 A		
Holding brake			
Holding brake version	Permanent-magnet brake		
Holding torque	22.0 Nm		
Power supply voltage	DC 24 V ± 10 %		
Coil current	0.9 A		
Opening time	200 ms		
Closing time	60 ms		
Highest braking work	1400 J		