

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1RA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data	
Rated speed (100 K)	3000 rpm
Number of poles	8
Rated torque (100 K)	6.8 Nm
Rated current	4.4 A
Static torque (60 K)	6.60 Nm
Static torque (100 K)	8.00 Nm
Stall current (60 K)	4.00 A
Stall current (100 K)	4.90 A
Moment of inertia	14.200 kgcm²
Efficiency	92.0 %
Physical constants	
Torque constant	1.61 Nm/A
Voltage constant at 20° C	105.0 V/1000*min ⁻¹
Winding resistance at 20° C	0.98 Ω
Rotating field inductance	17.2 mH
Electrical time constant	17.50 ms
Mechanical time constant	1.52 ms
Thermal time constant	40 min
Shaft torsional stiffness	120000 Nm/rad
Net weight of the motor	10.3 kg

Mechanical data	
Motor type	Permanent-magnet synchronous motor
Motor type	Compact
Shaft height	80
Cooling	Natural cooling
Radial runout tolerance	0.050 mm
Concentricity tolerance	0.10 mm
Axial runout tolerance	0.10 mm
Vibration severity grade	Grade A
Connector size	1
Degree of protection	IP64
Design acc. to Code I	IM B5 (IM V1, IM V3)
Temperature monitoring	Pt1000 temperature sensor
Electrical connectors	Connectors for signals and power rotatable
Color of the housing	Standard (Anthracite RAL 7016)
Holding brake	without holding brake
Shaft end	Feather key
Encoder system	Encoder AM20DQI: absolute encoder 20 bits (resolution 1048576, encoder-internal 512 S/R) + 12 bits multi-turn (traversing range 4096 revolutions)



Figure similar

MLFB-Ordering data 1FK7080-2AF71-1RA0

Optimum operating point		Recommended Motor Module	
Optimum speed	3000 rpm	Rated inverter current	5 A
Optimum power	2.1 kW	Maximum inverter current	15 A
Limiting data		Maximum torque	22.10 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	5500 rpm		
Maximum torque	25.0 Nm		
Maximum current	18.0 A		