

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data                      1FK7081-2AF74-1SH0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                               | Mechanical data          |                                                                                             |
|-----------------------------|-------------------------------|--------------------------|---------------------------------------------------------------------------------------------|
| Rated speed (100 K)         | 3000 rpm                      | Motor type               | Permanent-magnet synchronous motor                                                          |
| Number of poles             | 8                             | Motor type               | Compact                                                                                     |
| Rated torque (100 K)        | 8.7 Nm                        | Shaft height             | 80                                                                                          |
| Rated current               | 6.8 A                         | Cooling                  | Natural cooling                                                                             |
| Static torque (60 K)        | 10.00 Nm                      | Radial runout tolerance  | 0.050 mm                                                                                    |
| Static torque (100 K)       | 12.00 Nm                      | Concentricity tolerance  | 0.10 mm                                                                                     |
| Stall current (60 K)        | 7.10 A                        | Axial runout tolerance   | 0.10 mm                                                                                     |
| Stall current (100 K)       | 8.70 A                        | Vibration severity grade | Grade A                                                                                     |
| Moment of inertia           | 23.500 kgcm²                  | Connector size           | 1                                                                                           |
| Efficiency                  | 93.0 %                        | Degree of protection     | IP64                                                                                        |
| Physical constants          |                               | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                                                        |
| Torque constant             | 1.38 Nm/A                     | Temperature monitoring   | Pt1000 temperature sensor                                                                   |
| Voltage constant at 20° C   | 88.5 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable                                                  |
| Winding resistance at 20° C | 0.42 Ω                        | Color of the housing     | Standard (Anthracite RAL 7016)                                                              |
| Rotating field inductance   | 7.7 mH                        | Holding brake            | with holding brake                                                                          |
| Electrical time constant    | 18.20 ms                      | Shaft end                | Plain shaft                                                                                 |
| Mechanical time constant    | 1.35 ms                       | Encoder system           | Multi-pole resolver (number of pole pairs corresponds to number of pole pairs of the motor) |
| Thermal time constant       | 45 min                        |                          |                                                                                             |
| Shaft torsional stiffness   | 76000 Nm/rad                  |                          |                                                                                             |
| Net weight of the motor     | 15.9 kg                       |                          |                                                                                             |



Figure similar

MLFB-Ordering data                      1FK7081-2AF74-1SH0

| Optimum operating point           |                        | Recommended Motor Module |          |
|-----------------------------------|------------------------|--------------------------|----------|
| Optimum speed                     | 3000 rpm               | Rated inverter current   | 9 A      |
| Optimum power                     | 2.8 kW                 | Maximum inverter current | 27 A     |
| Limiting data                     |                        | Maximum torque           | 34.10 Nm |
| Max. permissible speed (mech.)    | 6000 rpm               |                          |          |
| Max. permissible speed (inverter) | 6000 rpm               |                          |          |
| Maximum torque                    | 37.0 Nm                |                          |          |
| Maximum current                   | 30.0 A                 |                          |          |
| Holding brake                     |                        |                          |          |
| Holding brake version             | Permanent-magnet brake |                          |          |
| Holding torque                    | 22.0 Nm                |                          |          |
| Power supply voltage              | DC 24 V ± 10 %         |                          |          |
| Coil current                      | 0.9 A                  |                          |          |
| Opening time                      | 200 ms                 |                          |          |
| Closing time                      | 60 ms                  |                          |          |
| Highest braking work              | 1400 J                 |                          |          |