

Data sheet for SIMOTICS S-1FK7



MLFB-Ordering data1FK7083-2AC71-1RH0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                                | Mechanical data          |                                                                                                                                                   |
|-----------------------------|--------------------------------|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated speed (100 K)         | 2000 rpm                       | Motor type               | Permanent-magnet synchronous motor                                                                                                                |
| Number of poles             | 8                              | Motor type               | Compact                                                                                                                                           |
| Rated torque (100 K)        | 12.5 Nm                        | Shaft height             | 80                                                                                                                                                |
| Rated current               | 6.3 A                          | Cooling                  | Natural cooling                                                                                                                                   |
| Static torque (60 K)        | 13.30 Nm                       | Radial runout tolerance  | 0.050 mm                                                                                                                                          |
| Static torque (100 K)       | 16.00 Nm                       | Concentricity tolerance  | 0.10 mm                                                                                                                                           |
| Stall current (60 K)        | 6.10 A                         | Axial runout tolerance   | 0.10 mm                                                                                                                                           |
| Stall current (100 K)       | 7.50 A                         | Vibration severity grade | Grade A                                                                                                                                           |
| Moment of inertia           | 29.500 kgcm²                   | Connector size           | 1                                                                                                                                                 |
| Efficiency                  | 93.0 %                         | Degree of protection     | IP64                                                                                                                                              |
| Physical constants          |                                | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                                                                                                              |
| Torque constant             | 2.13 Nm/A                      | Temperature monitoring   | Pt1000 temperature sensor                                                                                                                         |
| Voltage constant at 20° C   | 138.5 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable                                                                                                        |
| Winding resistance at 20° C | 0.66 Ω                         | Color of the housing     | Standard (Anthracite RAL 7016)                                                                                                                    |
| Rotating field inductance   | 12.8 mH                        | Holding brake            | with holding brake                                                                                                                                |
| Electrical time constant    | 19.40 ms                       | Shaft end                | Plain shaft                                                                                                                                       |
| Mechanical time constant    | 1.13 ms                        | Encoder system           | Encoder AM20DQI: absolute encoder 20 bits (resolution 1048576, encoder-internal 512 S/R) + 12 bits multi-turn (traversing range 4096 revolutions) |
| Thermal time constant       | 50 min                         |                          |                                                                                                                                                   |
| Shaft torsional stiffness   | 72000 Nm/rad                   |                          |                                                                                                                                                   |
| Net weight of the motor     | 18.6 kg                        |                          |                                                                                                                                                   |



Figure similar

MLFB-Ordering data                      1FK7083-2AC71-1RH0

| Optimum operating point           |                        | Recommended Motor Module |          |
|-----------------------------------|------------------------|--------------------------|----------|
| Optimum speed                     | 2000 rpm               | Rated inverter current   | 9 A      |
| Optimum power                     | 2.6 kW                 | Maximum inverter current | 27 A     |
| Limiting data                     |                        | Maximum torque           | 49.30 Nm |
| Max. permissible speed (mech.)    | 6000 rpm               |                          |          |
| Max. permissible speed (inverter) | 4150 rpm               |                          |          |
| Maximum torque                    | 50.0 Nm                |                          |          |
| Maximum current                   | 27.5 A                 |                          |          |
| Holding brake                     |                        |                          |          |
| Holding brake version             | Permanent-magnet brake |                          |          |
| Holding torque                    | 22.0 Nm                |                          |          |
| Power supply voltage              | DC 24 V ± 10 %         |                          |          |
| Coil current                      | 0.9 A                  |                          |          |
| Opening time                      | 200 ms                 |                          |          |
| Closing time                      | 60 ms                  |                          |          |
| Highest braking work              | 1400 J                 |                          |          |