SIEMENS

## Data sheet for SIMOTICS S-1FK7

**MLFB-Ordering data** **1FK7100-2AC74-1SH0**



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

### Engineering data

| | |
|---|---|
| Rated speed (100 K) | 2000 rpm |
| Number of poles | 8 |
| Rated torque (100 K) | 14.5 Nm |
| Rated current | 7.1 A |
| Static torque (60 K) | 14.90 Nm |
| Static torque (100 K) | 18.00 Nm |
| Stall current (60 K) | 6.80 A |
| Stall current (100 K) | 8.40 A |
| Moment of inertia | 62.000 kgcm² |
| Efficiency | 92.0 % |

### Physical constants

| | |
|---|---|
| Torque constant | 2.14 Nm/A |
| Voltage constant at 20° C | 138.0 V/1000*min⁻¹ |
| Winding resistance at 20° C | 0.55 Ω |
| Rotating field inductance | 12.7 mH |
| Electrical time constant | 23.00 ms |
| Mechanical time constant | 1.95 ms |
| Thermal time constant | 55 min |
| Shaft torsional stiffness | 135000 Nm/rad |
| Net weight of the motor | 21.0 kg |

### Mechanical data

| | |
|---|---|
| Motor type | Permanent-magnet synchronous motor |
| Motor type | Compact |
| Shaft height | 100 |
| Cooling | Natural cooling |
| Radial runout tolerance | 0.050 mm |
| Concentricity tolerance | 0.10 mm |
| Axial runout tolerance | 0.10 mm |
| Vibration severity grade | Grade A |
| Connector size | 1 |
| Degree of protection | IP64 |
| Design acc. to Code I | IM B5 (IM V1, IM V3) |
| Temperature monitoring | Pt1000 temperature sensor |
| Electrical connectors | Connectors for signals and power rotatable |
| Color of the housing | Standard (Anthracite RAL 7016) |
| Holding brake | with holding brake |
| Shaft end | Plain shaft |
| Encoder system | Multi-pole resolver (number of pole pairs corresponds to number of pole pairs of the motor) |

SIEMENS

**MLFB-Ordering data** **1FK7100-2AC74-1SH0**



Figure similar

## Optimum operating point

| | |
|---|---|
| Optimum speed | 2000 rpm |
| Optimum power | 3.0 kW |

## Limiting data

| | |
|---|---|
| Max. permissible speed (mech.) | 5000 rpm |
| Max. permissible speed (inverter) | 4200 rpm |
| Maximum torque | 55.0 Nm |
| Maximum current | 28.0 A |

## Holding brake

| | |
|---|---|
| Holding brake version | Permanent-magnet brake |
| Holding torque | 23.0 Nm |
| Power supply voltage | DC 24 V ± 10 % |
| Coil current | 1.0 A |
| Opening time | 300 ms |
| Closing time | 70 ms |
| Highest braking work | 3380 J |

## Recommended Motor Module

| | |
|---|---|
| Rated inverter current | 9 A |
| Maximum inverter current | 27 A |
| Maximum torque | 53.40 Nm |