

Data sheet for SIMOTICS S-1FK7



MLFB-Ordering data 1FK7105-2AF71-1UA2

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data		Mechanical data	
Rated speed (100 K)	3000 rpm	Motor type	Permanent-magnet synchronous motor
Number of poles	8	Motor type	Compact
Rated torque (100 K)	26.0 Nm	Shaft height	100
Rated current	18.0 A	Cooling	Natural cooling
Static torque (60 K)	40.00 Nm	Radial runout tolerance	0.050 mm
Static torque (100 K)	48.00 Nm	Concentricity tolerance	0.10 mm
Stall current (60 K)	25.00 A	Axial runout tolerance	0.10 mm
Stall current (100 K)	31.00 A	Vibration severity grade	Grade A
Moment of inertia	154.000 kgcm ²	Connector size	1.5
Efficiency	94.0 %	Degree of protection	IP65 and DE flange IP67
Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
Torque constant	1.55 Nm/A	Temperature monitoring	Pt1000 temperature sensor
Voltage constant at 20° C	102.0 V/1000*min ⁻¹	Electrical connectors	Connectors for signals and power rotatable
Winding resistance at 20° C	0.07 Ω	Color of the housing	Standard (Anthracite RAL 7016)
Rotating field inductance	1.9 mH	Holding brake	without holding brake
Electrical time constant	26.00 ms	Shaft end	Feather key
Mechanical time constant	1.40 ms	Encoder system	Resolver R15DQ: resolver 15 bits (resolution 32768, internal multi-pole)
Thermal time constant	70 min		
Shaft torsional stiffness	125000 Nm/rad		
Net weight of the motor	39.0 kg		



Figure similar

MLFB-Ordering data 1FK7105-2AF71-1UA2

Optimum operating point		Recommended Motor Module	
Optimum speed	3000 rpm	Rated inverter current	30 A
Optimum power	8.2 kW	Maximum inverter current	90 A
Limiting data		Maximum torque	129.70 Nm
Max. permissible speed (mech.)	5000 rpm		
Max. permissible speed (inverter)	5000 rpm		
Maximum torque	150.0 Nm		
Maximum current	109.0 A		