

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data                      1FK7100-2AF74-1TH0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                                | Mechanical data          |                                            |
|-----------------------------|--------------------------------|--------------------------|--------------------------------------------|
| Rated speed (100 K)         | 3000 rpm                       | Motor type               | Permanent-magnet synchronous motor         |
| Number of poles             | 8                              | Motor type               | Compact                                    |
| Rated torque (100 K)        | 12.0 Nm                        | Shaft height             | 100                                        |
| Rated current               | 8.0 A                          | Cooling                  | Natural cooling                            |
| Static torque (60 K)        | 14.90 Nm                       | Radial runout tolerance  | 0.050 mm                                   |
| Static torque (100 K)       | 18.00 Nm                       | Concentricity tolerance  | 0.10 mm                                    |
| Stall current (60 K)        | 9.00 A                         | Axial runout tolerance   | 0.10 mm                                    |
| Stall current (100 K)       | 11.10 A                        | Vibration severity grade | Grade A                                    |
| Moment of inertia           | 62.000 kgcm²                   | Connector size           | 1                                          |
| Efficiency                  | 92.0 %                         | Degree of protection     | IP64                                       |
| Physical constants          |                                | Design acc. to Code I    | IM B5 (IM V1, IM V3)                       |
| Torque constant             | 1.62 Nm/A                      | Temperature monitoring   | Pt1000 temperature sensor                  |
| Voltage constant at 20° C   | 104.5 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable |
| Winding resistance at 20° C | 0.32 Ω                         | Color of the housing     | Standard (Anthracite RAL 7016)             |
| Rotating field inductance   | 7.3 mH                         | Holding brake            | with holding brake                         |
| Electrical time constant    | 22.50 ms                       | Shaft end                | Plain shaft                                |
| Mechanical time constant    | 2.00 ms                        | Encoder system           | Resolver 2-pole                            |
| Thermal time constant       | 55 min                         |                          |                                            |
| Shaft torsional stiffness   | 135000 Nm/rad                  |                          |                                            |
| Net weight of the motor     | 21.0 kg                        |                          |                                            |



Figure similar

MLFB-Ordering data                      1FK7100-2AF74-1TH0

| Optimum operating point           |                        | Recommended Motor Module |          |
|-----------------------------------|------------------------|--------------------------|----------|
| Optimum speed                     | 3000 rpm               | Rated inverter current   | 18 A     |
| Optimum power                     | 3.8 kW                 | Maximum inverter current | 54 A     |
| Limiting data                     |                        | Maximum torque           | 55.00 Nm |
| Max. permissible speed (mech.)    | 5000 rpm               |                          |          |
| Max. permissible speed (inverter) | 5000 rpm               |                          |          |
| Maximum torque                    | 55.0 Nm                |                          |          |
| Maximum current                   | 37.0 A                 |                          |          |
| Holding brake                     |                        |                          |          |
| Holding brake version             | Permanent-magnet brake |                          |          |
| Holding torque                    | 23.0 Nm                |                          |          |
| Power supply voltage              | DC 24 V ± 10 %         |                          |          |
| Coil current                      | 1.0 A                  |                          |          |
| Opening time                      | 300 ms                 |                          |          |
| Closing time                      | 70 ms                  |                          |          |
| Highest braking work              | 3380 J                 |                          |          |